Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Rack PDU, Basic, Zero U, 5.7kW, 208V, (36)C13 & (6)C19

AP7564

Overview

Lead time Usually in Stock

Main

| Color | Black | |
|---------------------------|---|--|
| Product or Component Type | PDU | |
| PDU Type | Basic | |
| Cord length | 3 ft (0.9 m) | |
| Number of cables | 1 | |
| Provided Equipment | Installation guide Rack Mounting brackets Toolless Mounting Kit | |

Complementary

| Input Voltage | 208 V 3 phase | |
|--------------------------|-------------------------------------|--|
| Height | 70.00 in (177.8 cm) | |
| Width | 2.20 in (5.6 cm) | |
| Output Voltage | 208 V | |
| Depth | 1.73 in (4.4 cm) | |
| Net Weight | 12.02 lb(US) (5.45 kg) | |
| Mounting Location | Side | |
| Mounting preference | No preference | |
| Input Plug Type | NEMA L21-20P | |
| Mounting Mode | Rack-mounted | |
| Rack units | 0U | |
| Mounting position | Vertical | |
| Line Rated Current | 16 A | |
| Input current limits | 20 A | |
| Load Capacity | 5700 VA | |
| Input Frequency | 50/60 Hz | |
| Outlet type and quantity | 36 IEC 60320 C13 6 IEC 60320 C19 | |

Environment

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| Product Certifications | cUL Listed UL Listed | |
|---------------------------------------|--|--|
| Standards | CSA C22.2 No. 60950-1-03 UL 60950-1 | |
| Ambient air temperature for operation | 32113 °F (045 °C) | |
| Relative Humidity | 595 % | |
| Operating altitude | 010000 ft | |
| Ambient Air Temperature for Storage | -13149 °F (-2565 °C) | |
| Storage Relative Humidity | 595 % | |
| Storage altitude | 0 50000 ft (0 000000000 15240 000000000 m) | |

Ordering and shipping details

GTIN 731304207948

Packing Units

| Unit Type of Package 1 | PCE | |
|------------------------------|------------------------|--|
| Number of Units in Package 1 | 1 | |
| Package 1 Height | 84.02 in (213.4 cm) | |
| Package 1 Width | 5.00 in (12.7 cm) | |
| Package 1 Length | 5.98 in (15.2 cm) | |
| Package 1 Weight | 14.02 lb(US) (6.36 kg) | |

Contractual warranty

Warranty 2 years repair or replace



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

| ∇ Environmental footprint | |
|--|-------------------------------|
| Carbon footprint (kg CO2 eq, Total Life cycle) | 135 |
| Environmental Disclosure | Product Environmental Profile |

Use Better

| EU RoHS Directive | Compliant |
|-----------------------------|--------------------------|
| REACh Regulation | REACh Declaration |
| ☼ Energy efficiency | |
| Optimized Energy Efficiency | Energy efficient product |

Use Again

| ○ Repack and remanufacture | |
|-----------------------------|---|
| Circularity Profile | End of Life Information |
| Halogen content performance | Product contains halogen above thresholds |
| Take-back | Yes |