Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications



Wired, Sensor, NetBotz, Temperature & Humidity

AP9512THBLK

Overview

Lead time Usually in Stock

Main

Product or Component Type	Temperature and humidity sensor	
Range of Product	Netbotz	
Number of rack unit	0U	
Provided Equipment	Mounting pads	

Physical

Color	Black	
Height	2.52 in (6.4 cm)	
Width	1.50 in (3.8 cm)	
Depth	0.87 in (2.2 cm)	
Net Weight	0.24 lb(US) (0.11 kg)	
Mounting preference	No preference	
Mounting Mode	Rack-mounted	

Environmental

Ambient air temperature for operation	32113 °F (045 °C)	
Operating altitude	010000 ft	
Relative Humidity	095 %	
Ambient Air Temperature for Storage	5149 °F (-1565 °C)	
Storage altitude	030000 ft (0.00000000009144.0000000000 m)	
Storage Relative Humidity	095 %	

Ordering and shipping details

GTIN 731304205159

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.52 in (6.4 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Width	0.87 in (2.2 cm)	
Package 1 Length	3.50 in (8.9 cm)	
Package 1 Weight	0.31 lb(US) (0.14 kg)	

Contractual warranty

Warranty 3 years repair or replace



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability

0	Environmental	factorint
~	Environmental	HOOLDIIIL

Environmental Disclosure Product Environmental Profile

Use Better

EU RoHS Directive Compliant

Use Again

○ Repack and remanufacture	
Circularity Profile	End of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Take-back	No