

## APC Service Bypass Panel-200/208/240V 100A MBB Hardwire input (3) L6-30R (3) L6-20R output

SBP10KRMT4U

_				
( )	VP	rv	P	۱۸/

Lead time Usually in Stock

#### Main

mann	
Main Input Voltage	200 V 208 V
Product or Component Type	Bypass kit
Main Output Voltage	200 V 208 V
Other Output Voltage	240 V
Number of rack unit	4U
Provided Equipment	Installation guide Rack Mounting brackets User Manual
Range of Product	Maintenance Bypass Panels

### **Physical**

Color	Black
Height	7.01 in (17.8 cm)
Width	17.01 in (43.2 cm)
Depth	26.50 in (67.3 cm)
Net Weight	48.1008964404000 lb(US) (21.8181818181818 kg)
Mounting Location	Front
Mounting preference	Lower
Mounting Mode	Rack-mounted

#### Input

Input Frequency	50/60 Hz
Number of input connectors	1 Hard Wire 3-wire (2PH + G)
Permissible voltage	200240 V
Max line current	100 A
Input current limits	100 A
Load Capacity	20000 VA
Power factor	01

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

### **Output**

Max current draw	100 A
Number of power socket outlets	3 NEMA L6-20R 3 NEMA L6-30R
Protection Type	Circuit breaker
Efficiency	99 %

#### Conformance

Product Certifications	CSA GOST
	GOST

#### **Environmental**

Ambient air temperature for operation	-4122 °F (-2050 °C)
Relative Humidity	095 %
Operating altitude	015000 ft
Ambient Air Temperature for Storage	-40149 °F (-4065 °C)
Storage Relative Humidity	095 %
Storage altitude	050000 ft (0.000000000015240.0000000000 m)

# Ordering and shipping details

GTIN	731304212621

# **Packing Units**

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	12.01 in (30.5 cm)
Package 1 Width	39.02 in (99.1 cm)
Package 1 Length	24.02 in (61 cm)
Package 1 Weight	70.14714065 lb(US) (31.81818182 kg)

### **Contractual warranty**

Warranty	2 years (parts only)	
----------	----------------------	--



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

#### **Use Better**

EU RoHS Directive	Compliant	
REACh Regulation	REACh Declaration	
Use Again		
○ Repack and remanufacture		
Take-back	No	