

Cable, UPS Communications Smart Signalling (15' / 4.5m - DB-9 to DB-9 Serial)

AP9804

Overview

Lead time Usually in Stock

Main

Cable length	15 ft (4.6 m)	
Number of cables	1	
Product Compatibility	UPS	

Physical

Color	Black	
Net Weight	0.99 lb(US) (0.45 kg)	
Mounting Location	Front	
Mounting Mode	Not rack-mountable	
Connector B	SUB-D 9 male Smart Signaling	
Connector A	SUB-D 9 female Smart Signaling	

Output

Number of port

Environmental

Storage Relative Humidity	095 %	
Storage altitude	050000 ft (0.000000000015240.0000000000 m)	
Ambient air temperature for operation	32113 °F (045 °C)	
Relative Humidity	095 %	
Operating altitude	010000 ft	
Ambient Air Temperature for Storage	5113 °F (-1545 °C)	

Ordering and shipping details

GTIN 731304203001

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.02 in (22.9 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Width	2.01 in (5.1 cm)	
Package 1 Length	4.02 in (10.2 cm)	
Package 1 Weight	0.99 lb(US) (0.45 kg)	

Contractual warranty

Warranty 2 years repair or replace



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability

☑ Environmental footprint

Environmental Disclosure

Product Environmental Profile

Use Better

EU RoHS Directive	Compliant
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov

Use Again

○ Repack and remanufacture	
Circularity Profile	End of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Take-back	No