

Product data sheet

Specifications



APC Back-UPS Pro, 1500VA/ 865W, Tower, 120V, 10x NEMA 5-15R outlets, AVR, LCD, User Replaceable Battery

BR1500G

Overview

Lead time Usually in Stock

Main

Main Input Voltage	120 V AC 1 phase
Input Connection Type	NEMA 5-15P
Plug standard	NEMA 5-15P
Input Frequency	50/60 Hz +/- 3 Hz auto-sensing
Output voltage	120 V AC 1 phase
Rated power in W	865 W
rated power in VA	1500 VA
output connection type	5 NEMA 5-15R 5 NEMA 5-15R surge
USB Charging Port	None
Maximum configurable power in VA	1500 VA
Max Configurable Power (Watts)	865 W
Transfer Time	8ms typical : 12ms maximum
Topology	Line Interactive
Waveform Type	Stepped approximation to a sinewave
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains

Complementary

Battery Capacity	9.0 Ah
Battery Size	Lead-acid internal included
Control panel	Multi-function LCD status and control console
Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm
UPS connectivity	USB port
Let Through Voltage Rating	300 V
Surge energy rating	354 J
Filtering	Full time multi-pole noise filtering :5% of IEEE surge let-through : zero clamping response time: in
Cable length	6 ft (1.8 m)
Height	11.9 in (301 mm)



Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Width	4.4 in (112 mm)
Depth	15.04 in (382 mm)
Net Weight	26.7 lb(US) (12.1 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable
Two post mountable	0
USB compatible	Yes
Mounting mode	Tower
Number of power module filled slots	0
Number of power module free slots	0
Redundant	No
Range of Product	Back-UPS Pro
Product or Component Type	Uninterruptible power supply (UPS)

Environment

Product Certifications	NOM TÜV ENERGY STAR V2.0 (USA)
Equipment protection policy	Lifetime : \$150000
Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage altitude	0...5000 ft (0...1524 m)
Relative Humidity	0...95 %
Storage Relative Humidity	0...95 %
Acoustic level	45 dBA
Operating altitude	0...3000 ft

Batteries & Runtime

Run Time	View Runtime Graph 
Efficiency	View Efficiency Graph 
Battery Type	Lead-Acid battery
Battery Voltage	24 V
Battery graph comments	This graph is based on actual measured runtime data. All measurements were taken with new, fully charged batteries and a balanced resistive load (PF = 1.0). Actual runtimes may vary from the values of this graph. Actual runtimes are dependent on several variables including battery age, battery charge level, environmental conditions and characteristics of the connected load.
Extendable Run Time	0
Included Battery Modules	1
Battery Slots Empty	0
Typical recharge time	8 h
RBC Quantity	1
Battery Life	3...5 year(s)

Replacement battery [APCRBC124](#) 

Battery Charge Power (Watts) 23 W rated

Ordering and shipping details

Category 11309 - APC RESALE PRODUCTS

GTIN 731304268772

Returnability No

Country of origin PH

Packing Units

Unit Type of Package 1 PCE

Nbr. of units in pkg. 1

Package 1 Height 15.2 in (38.7 cm)

Package 1 Width 19.2 in (48.8 cm)

Package 1 Length 9.4 in (23.8 cm)

Package weight(Lbs) 29.43 lb(US) (13.35 kg)

SCC14 10731304268779

Contractual warranty

Warranty (in months) 12 Battery|36 UPS



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Total lifecycle Carbon footprint	476 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	128 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	1 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	345 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	1 kg CO2 eq.
Environmental Disclosure	Product Environmental Profile

Use Better



Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant By Exemption
REACH Regulation	Reference contains Substances of Very High Concern above the threshold
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov



Energy efficiency

Optimized Energy Efficiency	Energy efficient product
ENERGY STAR®	ENERGY STAR UPS V2.0 (USA)

Use Longer



Lifetime extension

Repair	No
--------	----

Use Again



Repack and remanufacture

Recyclability potential, in %	62
Circularity Profile	End of Life Information
Removable battery	User replaceable

Take-back

Yes

WEEE Label



The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Technical Illustration

Dimensions



Offer Marketing Illustration

Product benefits / Features



Robust battery to keep you on track

Reliable runtime allows you to continue critical activities when the power is out.

Offer Marketing Illustration

Product benefits / Features



Offer Marketing Illustration

Product benefits / Features



Power goes out. You stay connected to what matters.

Enjoy uninterrupted internet connection for your entertainment, smart home and security devices.

Offer Marketing Illustration

Product benefits / Features



Smaller and lighter than other Back-UPS models...
...to fit conveniently on the desk or under it.

Offer Marketing Illustration

Product benefits / Features

The image is a marketing illustration for the APC Back-UPS Pro BR1500G. It features the Schneider Electric logo at the top left, followed by the APC logo. The product name 'APC Back-UPS Pro' is written in a large green font, with the tagline 'Reliable battery backup and surge protection to keep you connected' below it. To the right is a vertical black tower-style UPS unit. Below the product name and tagline are five circular icons, each with a corresponding feature description: a bar chart for '1500VA/865W', a lightning bolt for 'Automatic Voltage Regulation', a battery pack for 'Extended battery pack', a power outlet for '10 NEMA 5-15R outlets', and a battery cell for 'User replaceable batteries'.

Life Is On | Schneider Electric

APC

APC Back-UPS Pro


Reliable battery backup and surge protection to keep you connected

- 1500VA/865W
- Automatic Voltage Regulation
- Extended battery pack
- 10 NEMA 5-15R outlets
- User replaceable batteries

Offer Marketing Illustration

Product benefits / Features

Complete power protection for every day



APC Back-UPS Pro automatically corrects voltage levels to deliver clean, consistent power, 24/7

so your devices perform better, last longer and stay connected during power outages.

Offer Marketing Illustration

Product benefits / Features



Offer Marketing Illustration

Product benefits / Features

Peace of mind at home or office with PowerChute™ Serial Shutdown Software

UPS management, graceful shutdown, and energy management software for:



Desktops



Servers



Workstations



Image of product / Alternate images

Alternative

