Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Rack PDU, Basic, Zero U, 10A, 230V, (15)C13



AP9568

Usually in Stock

Overview

Lead time

PDU Type

Main	
Color	Black
Product or Component Type	PDU

Cord length 6.5 ft (2.0 m)

Number of cables 1

Basic

Provided Equipment Installation guide
Rack Mounting brackets

Toolless Mounting Kit

Complementary

Complementary		
Input Voltage	120 V 200 V 208 V 230 V 240 V	
Height	24.02 in (61 cm)	
Width	1.73 in (4.4 cm)	
Output Voltage	208 V 230 V	
Depth	1.73 in (4.4 cm)	
Net Weight	4.4 lb(US) (2 kg)	
Mounting Location	Side	
Mounting preference	No preference	
Input Plug Type	IEC 60320 C14	
Mounting Mode	Rack-mounted	
Rack units	0U	
Mounting position	Vertical	
Permissible voltage	100240 V	
Input current limits	10 A	
Load Capacity	2300 VA	
Input Frequency	50/60 Hz	
Outlet type and quantity	15 IEC 60320 C13	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Environment

Product Certifications	cUL Listed CE GOST Queensland Australia UL Listed VDE	
Ambient air temperature for operation	32113 °F (045 °C)	
Relative Humidity	095 %	
Operating altitude	010000 ft	
Ambient Air Temperature for Storage	-13149 °F (-2565 °C)	
Storage Relative Humidity	095 %	
Storage altitude	050000 ft (0.000000000015240.0000000000 m)	

Ordering and shipping details

GTIN 731304207054

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	25.51 in (64.8 cm)
Package 1 Width	7.01 in (17.8 cm)
Package 1 Length	5.98 in (15.2 cm)
Package 1 Weight	6.005 lb(US) (2.724 kg)

Contractual warranty

Warranty 2 years repair or replace



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	51
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
EU RoHS Directive	Compliant
REACh Regulation	REACh Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
Optimized Energy Efficiency	Energy efficient product

Use Again

○ Repack and remanufacture	
Circularity Profile	End of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Halogen content performance	Product contains halogen above thresholds
Take-back	Yes