

Product data sheet

Specifications



APC Smart-UPS, Line Interactive,
2200VA, Rackmount 2U, 120V, 6x
NEMA 5-15R+2x NEMA 5-20R
outlets, SmartSlot, AVR, LCD

SMT2200RM2U

Overview

Presentation	Intelligent and efficient network power protection from entry level to scalable runtime. Ideal UPS for servers, point-of-sale, routers, switches, hubs and other network devices.
--------------	---

Main

Main input voltage	120 V AC 1 phase
Input connection	NEMA 5-20P
Efficiency at full load	75...154 V adjustable 82...143 V
Input frequency	50/60 Hz +/- 3 Hz auto-sensing
Output voltage	120 V AC 1 phase
Rated power in W	1920 W
Rated power in VA	1920 VA
Output connection	6 NEMA 5-15R 2 NEMA 5-20R
Harmonic distortion	Less than 5%
Maximum configurable power in VA	2200 VA
Maximum configurable power in W	1980 W
Transfer time	4ms typical : 8ms maximum
UPS topology	Line Interactive
Waveform type	Sine wave
Output frequency	50/60 Hz +/- 3 Hz sync to mains
Replacement battery	RBC43

Graphs

Run Time	View Runtime Graph
Efficiency	View Efficiency Graph

Complementary

Battery type	Lead-acid internal included
Control panel	Multi-function LCD status and control console
Emergency power off	Yes
Free slot	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Control panel	LED status display with on line : on battery : replace battery and overload indicators
Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm
UPS connectivity	Serial port USB port Available expansion slot
Surge energy rating	530 J
Number of rack unit	2U
Cable length	8 ft (2.4 m)
Number of cables	1
Color	Black
Height	3.4 in (86 mm)
Width	18.9 in (480 mm)
Depth	26.9 in (683 mm)
Product weight	93.28 lb(US) (42.31 kg)
Mounting location	Front
Mounting preference	Lower
Mounting mode	Rack-mounted
Two post mountable	0
USB compatible	Yes
Mounting mode	Rack-mounted with included kit
Provided equipment	CD with software Documentation CD Rack Mounting brackets Rack Mounting support rails Smart UPS signalling RS-232 cable USB cable
Number of power modules	0
Number of power module filled slots	0
Number of power module free slots	0
Redundant	No
Range of product	Smart-UPS
Product or component type	Uninterruptible power supply (UPS)

Environment

Product certification	CSA
Equipment protection policy	Lifetime : \$150000
Ambient air temperature for operation	32...104 °F (0...40 °C)
Ambient air temperature for storage	5...113 °F (-15...45 °C)
Storage altitude	0...50000 ft (0...15240 m)
Relative humidity	0...95 %
Storage relative humidity	0...95 %
Acoustic level	55 dBA
Heat dissipation	215 Btu/h

Operating altitude	0...10000 ft
--------------------	--------------

Batteries & Runtime

Battery type	Lead-Acid battery
Extendable runtime	0
Included battery module	0
Empty battery slot	0
Typical recharge time	3 h
RBC quantity	1
Battery life	3...5 year(s)
Battery charging power	164 W rated

Ordering and shipping details

Category	11309 - APC RESALE PRODUCTS
GTIN	731304279532
Returnability	No
Country of origin	PH

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	10.0 in (25.4 cm)
Package 1 Width	38.6 in (98 cm)
Package 1 Length	23.6 in (60 cm)
Package weight(Lbs)	109.64 lb(US) (49.73 kg)

Contractual warranty

Warranty (in months)	24 Battery 36 UPS
----------------------	-------------------

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

 Environmental footprint	
Total lifecycle Carbon footprint	3 030 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	1 645 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	0 kg CO2 eq.
Carbon footprint of the installation phase [A5]	19 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	1 362 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	5 kg CO2 eq.

Use Better

 Materials and Substances	
Average percentage of recycled plastic content	15 %
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
SCIP Number	0637234b-27c7-4e32-ae29-543dd4803a99
EU RoHS Directive	Compliant By Exemption
REACH Regulation	Reference contains Substances of Very High Concern above the threshold
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

 Energy efficiency	
Optimized Energy Efficiency	Energy efficient product

Use Again

 Repack and remanufacture	
Circularity Profile	End of Life Information
Removable battery	User replaceable
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Image of product / Alternate images

Alternative

