

# Product data sheet

Specifications

## Rack PDU, Basic, 1U, 30A, 208V, (4) C19s



AP9570

### Overview

Lead time	Usually in Stock
-----------	------------------

### Main

Color	Black
Product or Component Type	PDU
PDU Type	Basic
Cord length	10 ft (3.05 m)
Number of cables	1
Provided Equipment	Installation guide Rack Mounting brackets

### Complementary

Input Voltage	200 V 208 V 230 V
Height	1.73 in (4.4 cm)
Width	17.60 in (44.7 cm)
Output Voltage	208 V
Depth	2.52 in (6.4 cm)
Net Weight	6.02 lb(US) (2.73 kg)
Mounting Location	Front Rear
Mounting preference	No preference
Input Plug Type	NEMA L6-30P
Mounting Mode	Rack-mounted
Rack units	1U
Mounting position	Horizontal
Line Rated Current	24 A
Permissible voltage	200...240 V
Max line current	30 A
Input current limits	30 A
Load Capacity	4992 VA
Input Frequency	50/60 Hz

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Outlet type and quantity	4 IEC 60320 C19
--------------------------	-----------------

## Environment

Product Certifications	cUL Listed METI Denan PSE UL Listed
Standards	UL 60950
Ambient air temperature for operation	32...113 °F (0...45 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.0000000000...15240.0000000000 m)

## Ordering and shipping details

GTIN	731304213086
------	--------------

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.76 in (7 cm)
Package 1 Width	9.02 in (22.9 cm)
Package 1 Length	18.27 in (46.4 cm)
Package 1 Weight	8.51 lb(US) (3.86 kg)

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	70
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

Use Better

Materials and Substances	
<a href="#">EU RoHS Directive</a>	Compliant
REACH Regulation	<a href="#">REACH Declaration</a>

Energy efficiency	
Optimized Energy Efficiency	Energy efficient product

Use Again

Repack and remanufacture	
Circularity Profile	<a href="#">End of Life Information</a>
Halogen content performance	Product contains halogen above thresholds
Take-back	Yes