

Rack PDU, Basic, Zero U, 16A, 230V, (20) C13 & (4) C19, IEC C20

AP7552

Overview

Lead time	Usually in Stock

Main

Color	Black	
Product or Component Type	PDU	
PDU Type	Basic	
Cord length	10 ft (3.05 m)	
Number of cables	1	
Provided Equipment	Installation guide Rack Mounting brackets Toolless Mounting Kit	

Complementary

Input Voltage	200 V
	208 V
	230 V
	250 V
Height	63.74 in (161.9 cm)
Width	2.20 in (5.6 cm)
Output Voltage	230 V
Depth	1.73 in (4.4 cm)
Net Weight	10.71 lb(US) (4.86 kg)
Mounting Location	Side
Mounting preference	No preference
Input Plug Type	IEC 60320 C20
Mounting Mode	Rack-mounted
Rack units	0U
Mounting position	Vertical
Input current limits	16 A
Load Capacity	3680 VA
Input Frequency	50/60 Hz
Outlet type and quantity	20 IEC 60320 C13 4 IEC 60320 C19

Environment

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Product Certifications	CE GOST IRAM VDE	
Ambient air temperature for operation	32113 °F (045 °C)	
Relative Humidity	595 %	
Operating altitude	010000 ft	
Ambient Air Temperature for Storage	-13149 °F (-2565 °C)	
Storage Relative Humidity	595 %	
Storage altitude	050000 ft (0.000000000015240.0000000000 m)	

Ordering and shipping details

GTIN 731304207900

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	83.50 in (212.1 cm)
Package 1 Width	5.98 in (15.2 cm)
Package 1 Length	5.00 in (12.7 cm)
Package 1 Weight	12.694 lb(US) (5.758 kg)

Contractual warranty

Warranty 2 years repair or replace



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

⊘ Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	120
Environmental Disclosure	Product Environmental Profile

Use Better

EU RoHS Directive	Compliant
REACh Regulation	REACh Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
Optimized Energy Efficiency	Energy efficient product

Use Again

○ Repack and remanufacture	
Circularity Profile	End of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Halogen content performance	Product contains halogen above thresholds
Take-back	Yes