



The product images are for illustration purposes only. Actual product appearance, ports, keyboard layout, and accessories may vary by model.

- Intel Core Ultra 9 185H, 16C (6P + 8E + 2LPE) / 22T, Max Turbo up to 5.1GHz, 24MB Intel Smart Cache
- 1x 16GB SODIMM DDR5-5600
- 512GB SSD M.2 2242 PCIe 4.0x4 NVMe
- Integrated Intel Arc Graphics Functions as Intel Graphics
- Windows 11 Pro, English (US) / English (UK)
- Case color - Arctic Grey
- 1-year, Courier or Carry-in

Premier Support - A direct 24x7x365 line to our most elite technicians.

- 

Advanced technical support, 24x7x365, in more than 100 markets
- 

Comprehensive hardware & OEM software support
- 

Single point of contact for simplified end-to-end case management
- 

Technical Account Managers for proactive relationship and escalation management
- 

Priority on service delivery and repair parts
- 

Lenovo Service Connect Portal for customized reporting and product support

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
 - Onsite Support
- Technician Installed Customer
 - Replaceable Unit Service
 - International Warranty Upgrade

Recommended Accessories United Kingdom



Lenovo Wired VoIP Headset 5000 (Teams)

4XD1R88995



Lenovo Essential Wireless Combo Keyboard & Mouse Gen2 Black-UK English

4X31R64490



ThinkPad USB4 Dock 5000 (with 135W Adapter)

40BF0135UK

>> [View More Accessories](#)

Recommended Services

Best

3Y Premier Support for AIPC upgrade from 1Y Courier/Carry-in (5WS1U93921)

Better

5Y Onsite upgrade from 1Y Courier/Carry-in (5WS0E84924)

Good

3Y Onsite upgrade from 1Y Courier/Carry-in (5WS0A23681)

PERFORMANCE

Processor

Intel Core™ Ultra 9 185H, 16C (6P + 8E + 2LPE) / 22T, Max Turbo up to 5.1GHz, 24MB Intel® Smart Cache

AI PC Category

AI PC^[1]

NPU

Integrated Intel® AI Boost, up to 11 TOPS

Graphics

Integrated Intel® Arc™ Graphics Functions as Intel® Graphics

Chipset

Intel® SoC Platform

Memory

1x 16GB SODIMM DDR5-5600

Memory Slots

Two DDR5 SODIMM slots, dual-channel capable

Max Memory^[2]

Up to 64GB DDR5-5600

Storage

512GB SSD M.2 2242 PCIe® 4.0x4 NVMe®

Storage Slot

Two M.2 2280 PCIe® 4.0 x4 slots

Max Storage Support^[3]

Up to two drives, 2x M.2 SSD • M.2 2280 SSD up to 2TB each

Card Reader

SD Card Reader

Audio Chip

High Definition (HD) Audio, Realtek® ALC3287 codec

Speakers

Stereo speakers, 2W x2, Dolby Audio™

Microphone

2x, Array

Camera

FHD 1080p with Privacy Shutter

Battery

45Wh

Power Adapter

65W USB-C® Slim (2-pin, Wall-mount)

Special Features

Modern Standby

DESIGN

Display

16" WUXGA (1920x1200) IPS 300nits Anti-glare, 45% NTSC, 60Hz, Touch^[4]

Touchscreen

In-cell, 10-point Multi-touch

Screen-to-Body Ratio

90%

Color Calibration

No Color Calibration

Pen

Pen Not Supported

Keyboard

Backlit, English

Touchpad

Buttonless Mylar® surface multi-touch touchpad, supports Precision TouchPad (PTP), 75 x 120 mm (2.95 x 4.72 inches)

Dimensions (WxDxH)^[5]

356 x 253.5 x 17.5 mm (14.01 x 9.98 x 0.69 inches)

Weight^[6]

Starting at 1.7 kg (3.75 lbs)

Case Color

Arctic Grey

Case Material

Aluminium (Top), PC-ABS (Bottom)

Surface Treatment

Anodizing Sandblasting (Top), Texture (Bottom)

SOFTWARE

Operating System

Windows® 11 Pro, English (US) / English (UK)

Bundled Software

Office Trial

CONNECTIVITY

WLAN + Bluetooth

Intel® Wi-Fi® 6E AX211, 802.11ax 2x2 + BT5.3

WWAN

WWAN Not Supported

Ethernet

100/1000M (RJ-45)

Standard Ports

- 1x USB-A (USB 5Gbps / USB 3.2 Gen 1)
- 1x USB-A (USB 5Gbps / USB 3.2 Gen 1), Always On
- 1x USB-C® (USB 10Gbps / USB 3.2 Gen 2), with USB PD 45-65W and DisplayPort™ 1.4
- 1x USB-C® (Thunderbolt™ 4 / USB4® 40Gbps), with USB PD 45-65W and DisplayPort™ 2.1
- 1x HDMI® 2.1, up to 4K/60Hz
- 1x Headphone / microphone combo jack (3.5mm)
- 1x Ethernet (RJ-45)
- 1x SD card reader

Docking

Various docking solutions supported via Thunderbolt™ / USB-C®. For more compatible docking solutions, please visit [Docking for ThinkBook® 16 G8 IAL](#)

SECURITY & PRIVACY

Security Chip

Firmware TPM 2.0 Enabled

Physical Locks

Kensington Nano Security Slot™, 2.5 x 6 mm

Fingerprint Reader

Touch Style, Match-on-Chip, Integrated in Power Button

Other Security

Camera privacy shutter

MANAGEABILITY

System Management

Non-vPro®

SERVICE

Base Warranty

1-year, Courier or Carry-in

Included Upgrade

None

ACCESSORIES

Bundled Accessories

None

CERTIFICATIONS

Green Certifications

- ENERGY STAR® 9.0
- EPEAT™ Gold Registered^[7]
- ErP Lot 6/26
- RoHS compliant
- TCO Certified, generation 10

Mil-Spec Test

MIL-STD-810H military test passed

Other Certifications

TÜV Rheinland® Low Blue Light (Software Solution)

MODEL

TopSeller	: Yes	EAN / UPC / JAN: 199274549282
Announce Date:	2026-02-18	End of Support : 2031-09-27

Note:
[\[1\]](#) AI PCs have a NPU capable of 10+ TOPs to run the Copilot assistant by pressing the optional Microsoft Copilot key or using Win + C.

- Please refer to the official [Lenovo store website](#) or contact a local Lenovo sales representative or authorized business partner for current inventory and purchase options.
- Lenovo reserves the right to change specifications without notice.
 - California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>
- To view full note details, please visit the [web page](#).