

Product data sheet

Specifications



APC Symmetra LX 4kVA Power Module, 220/230/240V

SYPM4KI



Overview

Presentation	High density, double-conversion on-line power protection with scalable runtime.
Lead time	Usually in Stock

Main

Main Input Voltage	230 V 400 V 3 phase
Product or Component Type	Power module
Other Input Voltage	220 V 240 V 380 V 415 V
Main Output Voltage	230 V
Other Output Voltage	220 V 240 V
Rated power in W	2800 W
rated power in VA	4000 VA
Output connector type	Hard Wire 3-wire (H N + E) for 1 zone(s)
Number of rack unit	4U
Provided Equipment	Installation guide
Range of Product	Symmetra Power Module

Batteries & Runtime

Run Time	View Runtime Graph
Included Battery Modules	0
Battery Slots Empty	0
Additional information	Configurable for 220 : 230 or 240 nominal output voltage

Physical

Height	5.9 in (150 mm)
Width	9.8 in (250 mm)
Depth	22.2 in (565 mm)
Net Weight	33.07 lb(US) (15 kg)
Mounting Location	Front
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

USB compatible	No
----------------	----

Input

Input Frequency	45...65 Hz auto-sensing
-----------------	-------------------------

Efficiency at full load	155...276 V 1:1 290...480 V 3:1
-------------------------	------------------------------------

Input Power Factor at Full Load	0.98
---------------------------------	------

Output

Max Configurable Power (Watts)	2800 W
--------------------------------	--------

Output Frequency (sync to mains)	50 Hz +/- 0.1 % for 50 Hz nominal not synced 60 Hz +/- 0.1 % for 60 Hz nominal not synced
----------------------------------	--

Crest factor	Up to 5 : 1
--------------	-------------

Topology	Double Conversion Online
----------	--------------------------

Waveform Type	Sine wave
---------------	-----------

Conformance

Product Certifications	C-tick CE GOST VDE
------------------------	-----------------------------

Standards	EN 50091-1 EN 50091-2 EN 55022 Class A EN 55024 EN 60950 IEC 60950
-----------	---

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
---------------------------------------	-------------------------

Relative Humidity	0...95 %
-------------------	----------

Operating altitude	0...10000 ft
--------------------	--------------

Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
-------------------------------------	--------------------------

Storage Relative Humidity	0...95 %
---------------------------	----------

Storage altitude	0...15000 ft (0...4572 m)
------------------	---------------------------

Acoustic level	62 dBA
----------------	--------

Ordering and shipping details

GTIN	731304218883
------	--------------

Packing Units

Unit Type of Package 1	PCE
------------------------	-----

Nbr. of units in pkg.	1
-----------------------	---

Package 1 Height	17.3 in (43.9 cm)
------------------	-------------------

Package 1 Width	13.0 in (33 cm)
-----------------	-----------------

Package 1 Length	22.2 in (56.5 cm)
------------------	-------------------

Package weight(Lbs)	40.08 lb(US) (18.18 kg)
---------------------	-------------------------

Contractual warranty

Warranty (in months)

24



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Total lifecycle Carbon footprint	3 133 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	238 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	2 kg CO2 eq.
Carbon footprint of the installation phase [A5]	2 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	0 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	6 kg CO2 eq.

Use Better



Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
SCIP Number	A208548b-09a8-4680-97a6-ad17b46807b1
EU RoHS Directive	Compliant By Exemption
REACH Regulation	Reference contains Substances of Very High Concern above the threshold

Use Longer




Lifetime extension

Repair	No
--------	----

Use Again



Repack and remanufacture

Recyclability potential, in %	66
Circularity Profile	End of Life Information
Take-back	Yes
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.