



The product images are for illustration purposes only. Actual product appearance, ports, keyboard layout, and accessories may vary by model.

- AMD Ryzen AI 7 PRO 350 (8C / 16T, 2.0 / 5.0GHz, 8MB L2 / 16MB L3)
- 1x 48GB SODIMM DDR5-5600 Non-ECC
- 512GB SSD M.2 2280 PCIe 4.0x4 Performance NVMe Opal 2.0
- Integrated AMD Radeon 860M Graphics
- Windows 11 Pro, English (US) / English (UK)
- Case color - Black
- 1Y Premier Support Upgrade from 1Y Courier/Carry-in

Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Comprehensive hardware & OEM software support



Single point of contact for simplified end-to-end case management



Technical Account Managers for proactive relationship and escalation management



Priority on service delivery and repair parts



Lenovo Service Connect Portal for customized reporting and product support

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
 - Onsite Support
- Technician Installed Customer
 - Replaceable Unit Service
 - International Warranty Upgrade

Recommended Accessories UAE (United Arab Emirates)



ThinkPad Bluetooth Presenter Mouse (Aura Edition)
4Y51T62792




Lenovo USB-C 100W AC Adapter-EU
GX21V43585



Lenovo 16-inch Premium Clarity Privacy Filter for ThinkBook 16 Gen 4 (16:10)
4XJ1U03940



ThinkPad USB4 Dock 5000
40BF0100US



ThinkPad 2TB Performance PCIe Gen4 NVMe OPAL2 M.2 2280 SSD IV
4XB1T87555

>> [View More Accessories](#)

PERFORMANCE

Processor
AMD Ryzen™ AI 7 PRO 350 (8C / 16T, 2.0 / 5.0GHz, 8MB L2 / 16MB L3)

AI PC Category
Copilot+ PC, AI-Ready Workstations

NPU
Integrated AMD Ryzen™ AI, up to 50 TOPS

Graphics
Integrated AMD Radeon™ 860M Graphics

Chipset
AMD SoC Platform

Memory
1x 48GB SODIMM DDR5-5600 Non-ECC

Memory Slots
Two DDR5 SODIMM slots, dual-channel capable

Max Memory
Up to 96GB (2x 48GB DDR5 SODIMM)

Storage
512GB SSD M.2 2280 PCIe® 4.0x4 Performance NVMe® Opal 2.0

Storage Slot
One M.2 2280 PCIe® 4.0 x4 slot

Max Storage Support^[1]
One drive, up to 2TB M.2 2280 SSD

Card Reader
No card reader

Audio Chip
High Definition (HD) Audio, Realtek® ALC3287 codec

Speakers
Stereo speakers, 2W x2, Dolby Atmos®

Microphone
2x, Array

Camera
5.0MP + IR with Privacy Shutter and Human Presence Detection

Battery
52.5Wh

Power Adapter
65W USB-C® Slim GaN (3-pin)

DESIGN

Display
16" WUXGA (1920x1200) IPS 400nits Anti-glare, 45% NTSC

Touchscreen
None

Color Calibration
AICCP Color Calibration

Pen
Pen Not Supported

Keyboard
Backlit, English

Dimensions (WxDxH)^[2]
359.70 x 251.70 x 11.80/18.14 (front/rear), 23.5 (maximum) mm; 14.16 x 9.91 x 0.47/0.71 (front/rear), 0.93 (maximum) inches

Weight^[3]
Starting at 1.71 kg (3.77 lbs)

Case Color
Black

Case Material
PC + 20% CF + 50% GF + 30% PCC (Top), PC + 20% CF + 30% PCC (Bottom)

SOFTWARE

Operating System
Windows® 11 Pro, English (US) / English (UK)

Bundled Software
Lenovo® AI Now

CONNECTIVITY

WLAN + Bluetooth
MediaTek Wi-Fi® 7 MT7925, 802.11be 2x2 + BT5.4

WWAN
WWAN Not Supported

SIM Card
No physical SIM card inbox

Ethernet
100/1000M (RJ-45)

NFC
No NFC

Standard Ports
• 1x USB-A (USB 5Gbps / USB 3.2 Gen 1)
• 1x USB-A (USB 5Gbps / USB 3.2 Gen 1), Always On
• 2x USB-C® (Thunderbolt™ 4 / USB4® 40Gbps), with PD 3.0 and DisplayPort™ 1.4
• 1x HDMI® 2.1, up to 4K/60Hz
• 1x Headphone / microphone combo jack (3.5mm)
• 1x Ethernet (GbE RJ-45)
• 1x Kensington Nano Security Slot™

Optional Ports (configured)
None

Docking
Various docking solutions supported via Thunderbolt™ or USB-C®. For more compatible docking solutions, please visit [Docking for ThinkPad® P16s Gen 4 \(AMD\)](#)

SECURITY & PRIVACY

Security Chip
Discrete TPM 2.0 Enabled

Physical Locks
Kensington Nano Security Slot™, 2.5 x 6 mm

Smart Card Reader
No Smart Card Reader

Fingerprint Reader
Touch Style, Match-on-Chip, Integrated in Power Button

Other Security
• Bottom cover tamper detection
• Camera privacy shutter (camera models)
• Ultrasonic Human Presence Detection for IR camera
• IR camera for Windows® Hello (facial recognition)

MANAGEABILITY

System Management
AMD PRO Manageability

SERVICE

Base Warranty
1-year, Courier or Carry-in

Included Upgrade
1Y Premier Support Upgrade from 1Y Courier/Carry-in

ACCESSORIES

CERTIFICATIONS

ISV Certifications
Please visit [ISV certifications for Lenovo® Workstations](#)

Green Certifications
• ENERGY STAR® 9.0
• EPEAT™ Gold Registered^[4]
• RoHS compliant
• TCO Certified, generation 10

Mil-Spec Test
MIL-STD-810H military test passed

Other Certifications
UL Low Blue Light

MODEL

TopSeller	: Yes	EAN / UPC / JAN: 199275502613
Announce Date: 2026-03-03		End of Support : 2031-11-22

- Please refer to the official [Lenovo store website](#) or contact a local Lenovo sales representative or authorized business partner for current inventory and purchase options.
 - Lenovo reserves the right to change specifications without notice.
 - California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>
- To see more note information, please access the [web page](#).