



The product images are for illustration purposes only. Actual product appearance, ports, keyboard layout, and accessories may vary by model.

- Intel Core Ultra 7 355, 8C (4P + 4LPE) / 8T, Max Turbo up to 4.7GHz, 12MB Intel Smart Cache
- 32GB Soldered LPDDR5X-7467
- 512GB SSD M.2 2280 PCIe 4.0x4 NVMe Opal 2.0
- Integrated Intel Graphics
- Windows 11 Pro, English (US) / English (UK)
- Case color - Blue
- 3Y Premier Support Upgrade from 3Y Courier/Carry-in, CO2 Offset Service 200kg Gen 3 Commercial IDG

Premier Support - A direct 24x7x365 line to our most elite technicians.

- 

Advanced technical support, 24x7x365, in more than 100 markets
- 

Comprehensive hardware & OEM software support
- 

Single point of contact for simplified end-to-end case management
- 

Technical Account Managers for proactive relationship and escalation management
- 

Priority on service delivery and repair parts
- 

Lenovo Service Connect Portal for customized reporting and product support

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
 - Onsite Support
- Technician Installed Customer
 - Replaceable Unit Service
 - International Warranty Upgrade

Recommended Accessories United States of America



Lenovo Wireless Multi-Mode Mechanical Keyboard 8000-US English
4Y41V37344



ThinkPad Dual-Mode Wireless ANC Foldable Headset 8550 (Aura Edition) - USB-A,...
4XD1V23301



ThinkPad 16" Click-Go Backpack (Aura Edition)
4X41V20931

>> [View More Accessories](#)

Recommended Services

Best

5Y Premier Support for AIPC upgrade from 3Y Premier Support (5WS1U94073)

Better

3Y Premier Support Plus for AIPC upgrade from 3Y Premier Support (5WS1U94043)

Good

4Y Premier Support for AIPC upgrade from 3Y Premier Support (5WS1U94072)

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

PERFORMANCE

Processor

Intel Core™ Ultra 7 355, 8C (4P + 4LPE) / 8T, Max Turbo up to 4.7GHz, 12MB Intel® Smart Cache

AI PC Category

Copilot+ PC^[1]

NPU

Up to 49 TOPS

Graphics

Integrated Intel® Graphics

Chipset

Intel® SoC Platform

Memory

32GB Soldered LPDDR5X-7467^[2]

Memory Slots

Memory soldered to systemboard, no slots, dual-channel

Max Memory

32GB soldered memory, not upgradable

Storage

512GB SSD M.2 2280 PCIe® 4.0x4 NVMe® Opal 2.0

Storage Slot

One M.2 2280 PCIe® 5.0 x4 slot

Max Storage Support^[3]

One drive, up to 2TB M.2 2280 SSD

Card Reader

No Card Reader

Audio Chip

SoundWire®, Realtek® ALC3346 codec

Speakers

Stereo speakers, 2W x2, Dolby Atmos®

Microphone

2x, 360°

Camera

5.0MP + IR Discrete with Privacy Shutter, vHDR, Computer Vision on ISP

Battery

58Wh

Power Adapter

65W USB-C® (3-pin)

DESIGN

Display

14" WUXGA (1920x1200) IPS 500nits Anti-glare, 100% sRGB, 60Hz, Low Power, Touch^[4]

Touchscreen

In-cell, 10-point Multi-touch

Screen-to-Body Ratio

88%

Pen

Pen Not Supported

Keyboard

Backlit, English

Dimensions (WxDxH)^[5]

313 x 219.4 x 10.7/15.85 (front/rear), 18.56 (maximum) mm 12.32 x 8.64 x 0.42/0.62 (front/rear), 0.73 (maximum) inches

Weight^[6]

Starting at 1.065 kg (2.35 lbs)

Case Color

Blue

Case Material

Carbon Fiber Hybrid (Top), Aluminium (Bottom)

SOFTWARE

Operating System

Windows® 11 Pro, English (US) / English (UK)

Bundled Software

Lenovo® AI Now

CONNECTIVITY

WLAN + Bluetooth

Intel® Wi-Fi® 7 BE211, 802.11be 2x2 + BT5.4

WWAN

WWAN Not Supported

SIM Card

No physical SIM card included

Ethernet

No Onboard Ethernet^[7]

NFC

No NFC

Standard Ports

- 1x USB-A (USB 5Gbps), Always On
- 3x Thunderbolt™ 4, with USB PD 15-65W and DisplayPort™ 2.1
- 1x HDMI® 2.1, up to 4K/60Hz
- 1x Headphone / microphone combo jack (3.5mm)

Optional Ports (configured)

None

Docking

Various docking solutions supported via Thunderbolt™ / USB-C®. For more compatible docking solutions, please visit [Docking for ThinkPad® T14s Gen 7 \(Intel®\)](#)

SECURITY & PRIVACY

ThinkShield

ThinkShield is a comprehensive security solution that encompasses hardware, software, and supply chain components. For more detials, visit [here](#)

Security Chip

Discrete TPM 2.0 Enabled

Physical Locks

Kensington Nano Security Slot™, 2.5 x 6 mm

Smart Card Reader

No Smart Card Reader

Fingerprint Reader

Touch Style, Match-on-Chip, Integrated in Power Button

Other Security

- Computer Vision-based Human Presence Detection on Image Signal Processor (ISP)
- Camera privacy shutter
- IR camera for Windows® Hello (facial recognition)

MANAGEABILITY

System Management

Non-vPro®

SERVICE

Base Warranty

3-year, Courier or Carry-in with 1-year Battery

Included Upgrade

3Y Premier Support Upgrade from 3Y Courier/Carry-in, CO2 Offset Service 200kg Gen 3 Commercial IDG

ACCESSORIES

Bundled Accessories

None

CERTIFICATIONS

Green Certifications

- ENERGY STAR® 9.0
- EPEAT™ Gold Registered^[8]
- ErP Lot 6/26
- RoHS compliant
- TCO Certified, generation 10

Mil-Spec Test

MIL-STD-810H military test passed

Other Certifications

Eyesafe® Certified 2.0

MODEL

TopSeller	: Yes	EAN / UPC / JAN: 199275822346
Announce Date:	2026-04-30	End of Support : 2032-11-30

Note:

^[1] Copilot+ PCs have at least 16GB RAM, 256GB storage, and a NPU that runs 40+ TOPs to run the latest AI tools build-in latest Windows 11 to accelerate productivity and creativity.
^[2] Installed memory is actually LPDDR5X-8533 but runs as LPDDR5X-7467 due to platform limitation.
^[3] The storage capacity supported is based on the test results with current Lenovo storage offerings.

- Please refer to the official [Lenovo store website](#) or contact a local Lenovo sales representative or authorized business partner for current inventory and purchase options.
- Lenovo reserves the right to change specifications without notice.
- To view full note details, please visit the [web page](#).