



# HyperX OMEN 35L Gaming Desktop GT18-0005a PC (D89SPPA)

## Overview

### Lose the Noise, Dominate the Game.

The HyperX OMEN 35L Gaming Desktop PC unlocks your performance potential. It features the latest Intel® Core™ Ultra Processor[1] and advanced graphics, with HyperX branded components optimized for peak thermal capabilities and power. Designed for easy tool-less upgradeability and personalization to suit your gaming needs.



### Optimized for Performance.

Play to your highest potential with a design that is optimized for performance.



### Make it your own.

Customize performance and aRGB options with OMEN Gaming Hub



### Futureproof, tool-less design.

Designed for upgradability with industry standard HyperX Components tested and calibrated for reliable performance.



### We're In This Together.

It matters. With 100% recyclable packaging solutions[2], at least 20% recycled plastic content and 10% recycled metal[3][4], we are in this together[5].

# Features



## Get a fresh perspective

From a rejuvenated Start menu, to new ways to connect to your favorite people, news, games, and content—Windows 11 is the place to think, express, and create in a natural way.<sup>[6]</sup>



## 1TB PCIe® Gen4 NVMe™ M.2 SSD

With high-speed data transfer, the 1 TB PCIe Gen4 NVMe M.2 SSD offers lightning fast speed and efficient storage.<sup>[8]</sup>



## Ethernet port

When you have a spotty wireless connection, you can quickly plug in your Ethernet cable to get a smooth, wired Internet experience that bypasses any wireless issue.



## Game Changer

Powered by NVIDIA Blackwell, GeForce RTX™ 50 Series GPUs bring game-changing AI capabilities to gamers and creators. Multiply performance with NVIDIA DLSS 4, generate images at unprecedented speed, and unleash your creativity with NVIDIA Studio.<sup>[7]</sup>



## USB Type-C® 10Gbps signaling data rate

Plug in your external storage with this USB Type-C® port, featuring 10Gbps signaling data rate. And it's reversible, so you never have to worry about plugging in upside down.<sup>[9]</sup>



## Realtek Wi-Fi 7 and Bluetooth® 6.0 wireless card

Take a leap in wireless performance with new levels of increased speed and reduced latency with Wi-Fi 7. Paired with Bluetooth® 6.0.<sup>[10]</sup>

---

[1] Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance. Intel and the Intel logo are trademarks of Intel Corporation or its subsidiaries in the U.S. and/or other countries.

[2] Packaging parts contain certified or recycled fibers and are typically recycled in your local paper/carton recycling bin, consult your local guidelines.

[3] Recycled plastic is expressed as a percentage of the total weight plastic. Post-consumer recycled is based on the definition set in the EPEAT standard for computers, IEEE 1680.1-2018 standard.

[4] Recycled metal is expressed as a percentage of the total weight of the metal according to ISO 14021 definitions for metal parts over 25 grams.

[5] Recycling facilities not available in all locations.

[6] Not all features are available in all editions or versions of Windows. Systems may require upgraded and/or separately purchased hardware, drivers, software or BIOS update to take full advantage of Windows functionality. Windows is automatically updated and enabled. High speed internet and Microsoft account required. ISP fees may apply and additional requirements may apply over time for updates. See <http://www.windows.com>.

[7] ©2025 NVIDIA Corporation. NVIDIA, the NVIDIA logo, GeForce, and GeForce RTX are registered trademarks and/or trademarks of NVIDIA Corporation in the United States and other countries. All

*other trademarks and copyrights are the property of their respective owners.*

*[8] For hard drives, GB = 1 billion bytes. TB = 1 trillion bytes. Actual formatted capacity is less. Up to 35GB of system disk is reserved for system recovery software.*

*[9] Actual throughput may vary. USB Type-C® and USB-C® are trademarks of USB Implementers Forum.*

*[10] Wireless access point and internet service required and sold separately. Availability of public wireless access points limited. Wi-Fi 7 is backwards compatible with prior Wi-Fi 6E specs. Bluetooth® is a trademark owned by Bluetooth SIG inc. and used by HP Inc. under license.*

## Specifications

<b>Form Factor</b>	microATX
<b>Operating System Software</b>	Windows 11 Home
<b>Product Color Description (fixed)</b>	Black
<b>Processor Family</b>	Intel® Core™ Ultra 7 processor
<b>Processor Name</b>	Intel® Core™ Ultra 7 270K Plus (up to 5.4 GHz with Intel® Turbo Boost Technology, 36 MB L3 cache, 24 cores, 24 threads) <sup>[6,7]</sup>
<b>Chipset</b>	Intel® Z890
<b>Standard Memory Description 01</b>	Kingston FURY 32 GB DDR5-6000 MT/s XMP RGB Heatsink (2 x 16 GB)
<b>Memory Slots</b>	4 DIMM
<b>Hard Drive Description (01)</b>	1 TB PCIe® Gen4 NVMe™ M.2 SSD
<b>Product Design</b>	Textured finish
<b>Graphics Card Segment 02</b>	Discrete
<b>GScardseg 02 Available Card 01</b>	NVIDIA® GeForce RTX™ 5070 Ti (16 GB GDDR7 dedicated)
<b>Audio Features</b>	Omen Audio Control Support DTS:X Ultra; 5.1 Channel audio support
<b>Product Dimensions (metric)</b>	21 x 40.8 x 41 cm
<b>Product Dimensions (imperial)</b>	8.27 x 16.06 x 16.14 in
<b>Weight (metric)</b>	14.5 kg
<b>Weight (imperial)</b>	31.97 lb
<b>Video Connectors</b>	1 HDMI 2.1b;3 DisplayPort™ 2.1b
<b>External I/O Ports</b>	1 USB Type-C® 10Gbps signaling rate (HP Sleep and Charge); 2 USB Type-A 5Gbps signaling rate (HP Sleep and Charge); 1 headphone/microphone combo <sup>[19]</sup>
<b>Expansion Slots</b>	3 M.2 (2 for SSD, 1 for WLAN); 1 PCIe Gen5 x16; 1 PCIe Gen5 x4
<b>External I/O Ports 02</b>	1 USB Type-C® 10Gbps signaling rate; 2 USB Type-A 5Gbps signaling rate (charging); 4 USB 2.0 Type-A; 1 microphone; 1 RJ-45; 1 microphone-in; 1 line in; 1 line out; 1 Thunderbolt™ 4 with USB Type-C® 40Gbps signaling rate (DisplayPort™ 2.1)
<b>Package Dimensions (metric)</b>	59 x 33.2 x 58.3 cm
<b>Package Weight (metric)</b>	18.5 kg
<b>Network Interface</b>	Realtek RTL8125BGH-CG 10/100/1000/2500 GbE NIC
<b>Wireless Technologies</b>	Realtek Wi-Fi 7 (2x2) and Bluetooth® 6.0 wireless card <sup>[12,46]</sup>
<b>Power Supply Type</b>	850 W 80 Plus Gold certified ATX 3.1 fully modular power supply
<b>Energy Star Certified</b>	ENERGY STAR® certified
<b>Sustainable Impact Specifications</b>	Water based paint; At least 10% recycled metal; LDPE bag contains 30% recycled plastic; Molded paper pulp cushion inside box is made of 100% recycled or certified sources; Contains post-consumer recycled plastic

<b>Security Management</b>	Kensington Security lock slot; Padlock
<b>Software Included</b>	McAfee Online Protection 30-day trial
<b>Software - Productivity &amp; Finance</b>	1 month trial for new Microsoft 365 customers <sup>[24,49,50]</sup>
<b>Cloud Service</b>	100 GB Dropbox storage for 3 months <sup>[1]</sup>
<b>UPC Number</b>	821844463253

## Additional specifications

<b>Bluetooth Version</b>	Bluetooth® 6.0
<b>Color</b>	Black glass
<b>DisplayPort™</b>	3
<b>DisplayPort™ version</b>	2.1b
<b>ECC Memory</b>	non-ECC
<b>Ecolabels</b>	EPEAT® Silver with Climate+; EPEAT® Gold with Climate+
<b>Ethernet (RJ-45)</b>	1
<b>Graphics Discrete Brand</b>	NVIDIA®
<b>Graphics Discrete Family</b>	GeForce
<b>Graphics Discrete Memory Size</b>	16
<b>Graphics Discrete Memory Size UOM</b>	GB
<b>Graphics Discrete Memory Type</b>	GDDR7
<b>Graphics Discrete Model Number</b>	RTX™ 5070 Ti
<b>HDMI version</b>	2.1b
<b>HDMI –out</b>	1
<b>Headphone/microphone combo</b>	1
<b>I/O Port Location 01</b>	Top
<b>I/O Port Location 02</b>	Rear
<b>Maximum Memory</b>	Supports up to 128 GB max system memory
<b>Memory Brand</b>	Kingston FURY
<b>Memory Layout (Slots &amp; Size)</b>	2 x 16 GB
<b>Memory Lighting</b>	RGB
<b>Memory Module Type</b>	UDIMM
<b>Memory Profile Technology</b>	XMP
<b>Memory Size</b>	32
<b>Memory Size UOM</b>	GB
<b>Memory Slots Number</b>	2
<b>Memory Speed</b>	6000
<b>Memory Speed UOM</b>	MT/s
<b>Memory Storage Simplified</b>	32 GB memory;1 TB SSD storage
<b>Memory Type</b>	DDR5
<b>Neural Processing Unit (NPU)</b>	Intel® AI Boost (13 NPU TOPS)
<b>Package Dimensions (imperial)</b>	23.23 x 13.07 x 22.95 in

<b>Package Weight (imperial)</b>	40.79 lb
<b>Processor Brand</b>	Intel®
<b>Processor Cache Installed</b>	36 MB L3
<b>Processor Core</b>	24
<b>Processor Family (Short)</b>	Core™ Ultra 7
<b>Processor Frequency Technology</b>	Intel® Turbo Boost Technology
<b>Processor Maximum Frequency</b>	5.4
<b>Processor Maximum Frequency UOM</b>	GHz
<b>Processor Model</b>	270K
<b>Processor NPU Tops</b>	13
<b>Processor Socket</b>	LGA1851
<b>Processor Threads</b>	24
<b>Product Brand Name</b>	HP
<b>Product Long Name Specifications</b>	HyperX OMEN 35L Gaming Desktop GT18-0005a PC, Windows 11 Home, Intel® Core™ Ultra 7, 32GB RAM, 1TB SSD, NVIDIA® GeForce RTX™ 5070 Ti, Black glass
<b>Product Long Name Specifications V2</b>	Windows 11 Home, Intel® Core™ Ultra 7, 32GB RAM, 1TB SSD, NVIDIA® GeForce RTX™ 5070 Ti, Black glass
<b>Product Short Name Specifications</b>	HyperX OMEN 35L Gaming Desktop GT18-0005a PC, Intel® Core™ Ultra 7, 32GB RAM, 1TB SSD
<b>Storage Capacity 01</b>	1
<b>Storage Capacity UOM 01</b>	TB
<b>Storage Form Factor 01</b>	M.2
<b>Storage Interface 01</b>	PCIe® Gen 4
<b>Storage Interface Protocol 01</b>	NVMe™
<b>Storage Type 01</b>	SSD
<b>Storage type (filter)</b>	SSD
<b>System Coolers</b>	240 mm LCD liquid cooler
<b>Thunderbolt™ 4 ports</b>	1
<b>UNSPSC Code</b>	43211507
<b>USB Type-A</b>	8
<b>USB Type-C</b>	2
<b>Wireless Antenna</b>	2x2
<b>Wireless Standard</b>	Wi-Fi 7
<b>Wireless Supplier</b>	Realtek

---

[1] 100 GB of free Dropbox storage for 3 months from date of registration. For complete details and terms of use, including cancellation policies, visit the Dropbox website at <https://www.dropbox.com/help/space/hp-promotion>. Internet service required and not included.

[6] Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.

[7] Intel® Turbo Boost performance varies depending on hardware, software and overall system configuration. See <http://www.intel.com/technology/turboboost/> for more information.

[12] Wireless access point and Internet service required and sold separately. Availability of public wireless access points limited. Wi-Fi 7 (802.11BE) functionality requires Windows 11 2024, select Intel® Core™ or Intel® Core™ Ultra processor, and a Wi-Fi 7 router, sold separately. Wi-Fi 7 is backwards compatible with prior 802.11 specs. Available in countries where Wi-Fi 7 is supported. The specification for 802.11BE is a draft specification and is not final. If the final specification differs from the draft specification, it may affect the ability of the device to communicate with other 802.11BE devices.

[19] NOTE: Please make sure the USB Charging mode is enabled in the BIOS settings to activate the "HP Sleep and Charge" feature.

[24] Must activate within 180 days of Windows activation.

[46] Bluetooth® 6.0 operation requires Microsoft OS/Chrome OS support. Until Microsoft OS/Chrome OS support is available, Bluetooth® 6.0 will function as Bluetooth® 5.4 or lower.

[49] Some Windows 11 features require camera, microphone, speakers and/or advanced hardware. Check [www.microsoft.com/windows](http://www.microsoft.com/windows) and/or [www.hp.com](http://www.hp.com) for details.

---

# HyperX Gaming Peripherals

## HyperX Earbuds

★ : Recommended

### HyperX Cloud Earbuds SC

HyperX Cloud Earbuds III S Black

BN7S1AA

HyperX Cloud Earbuds III S Red

BN7S2AA

## HyperX Gaming Headsets

### HyperX Cloud Stinger Headsets SC

HyperX Cloud Stinger 3 Gaming Headset

BS1T5AA

## HyperX Gaming Controllers

### HyperX Clutch Controllers SC

HyperX Clutch Tachi - Xbox

B11D9AA

## HyperX Gaming Keyboards

### HyperX Origins 2 Keyboards SC

HyperX Origins 2 Pro 65

BN7S3AA

# Monitors

## HP Home Monitors

★ : Recommended

### OMEN by HP Displays

HyperX OMEN 23.8 inch FHD 180Hz Gaming Monitor - OMEN 24 G2	C2JP4AA
HyperX OMEN 23.8 inch FHD 180Hz Gaming Monitor - OMEN 24 G2	C2JP4AS
HyperX OMEN 23.8 inch FHD 180Hz Gaming Monitor - OMEN 24 G2	C2JP4E9
HyperX OMEN OLED 27 inch QHD 240Hz Gaming Monitor - OMEN OLED 27q	CH0R2AA
HyperX OMEN OLED 27 inch QHD 240Hz Gaming Monitor - OMEN OLED 27q	CH0R2AS
HyperX OMEN OLED 27 inch QHD 240Hz Gaming Monitor - OMEN OLED 27q	CH0R2E9
HyperX OMEN OLED 27 inch QHD 500Hz Gaming Monitor - OMEN OLED 27qs	BY8Z1AA
HyperX OMEN OLED 27 inch QHD 500Hz Gaming Monitor - OMEN OLED 27qs	BY8Z1AS
HyperX OMEN OLED 27 inch QHD 500Hz Gaming Monitor - OMEN OLED 27qs	BY8Z1E9
OMEN 24.5inch FHD 360Hz Gaming Monitor - OMEN 25	BG1M4AA
OMEN 24.5inch FHD 360Hz Gaming Monitor - OMEN 25	BG1M4E9
OMEN 27 inch FHD 180Hz Gaming Monitor - OMEN 27 G2	AV4K1AA
OMEN 27 inch FHD 180Hz Gaming Monitor - OMEN 27 G2	AV4K1AS
OMEN 27 inch FHD 180Hz Gaming Monitor - OMEN 27 G2	AV4K1E9
OMEN 27 inch FHD 180Hz Gaming Monitor - OMEN 27 G2	AV4K2A6
OMEN 27 inch FHD 180Hz Gaming Monitor - OMEN 27 G2	AV4K2AA
OMEN 27 inch QHD 180Hz Gaming Monitor - OMEN 27q G2	AV4H6AA
OMEN 27 inch QHD 180Hz Gaming Monitor - OMEN 27q G2	AV4H6AS
OMEN 27 inch QHD 180Hz Gaming Monitor - OMEN 27q G2	AV4H6E9
OMEN 27 inch QHD 180Hz Gaming Monitor - OMEN 27q G2	AV4H7A6
OMEN 27 inch QHD 180Hz Gaming Monitor - OMEN 27q G2	AV4H7AA
OMEN 27 inch QHD 280Hz Gaming Monitor - OMEN 27qs G2	AW3V0AA
OMEN 27 inch QHD 280Hz Gaming Monitor - OMEN 27qs G2	AW3V0AS
OMEN 27 inch QHD 280Hz Gaming Monitor - OMEN 27qs G2	AW3V0E9
OMEN 27 inch QHD 280Hz Gaming Monitor - OMEN 27qs G2	AW3V1A6
OMEN 27 inch QHD 280Hz Gaming Monitor - OMEN 27qs G2	AW3V1AA
OMEN 34 inch WQHD 180Hz Curved Gaming Monitor - OMEN 34c G2	AV4C1AA
OMEN 34 inch WQHD 180Hz Curved Gaming Monitor - OMEN 34c G2	AV4C1AS
OMEN 34 inch WQHD 180Hz Curved Gaming Monitor - OMEN 34c G2	AV4C1E9
OMEN 34 inch WQHD 180Hz Curved Gaming Monitor - OMEN 34c G2	AV4E7A6

OMEN 34 inch WQHD 180Hz Curved Gaming Monitor - OMEN 34c G2	AV4E7AA	
OMEN Transcend 31.5 inch UHD 240Hz OLED Gaming Monitor - OMEN Transcend 32	9R181AA	
OMEN Transcend 31.5 inch UHD 240Hz OLED Gaming Monitor - OMEN Transcend 32	9R181E9	
OMEN by HP 23.8 inch FHD 165Hz Gaming Monitor - OMEN 24	780D9AA	
OMEN by HP 23.8 inch FHD 165Hz Gaming Monitor - OMEN 24	780D9AS	
OMEN by HP 23.8 inch FHD 165Hz Gaming Monitor - OMEN 24	780D9E9	
OMEN by HP 23.8 inch FHD 165Hz Gaming Monitor - OMEN 24	780F0A6	
OMEN by HP 23.8 inch FHD 165Hz Gaming Monitor - OMEN 24	780F0AA	
OMEN by HP 27 inch FHD 165Hz Gaming Monitor - OMEN 27	780F9AA	
OMEN by HP 27 inch FHD 240Hz Gaming Monitor - OMEN 27s	780G5AA	obsolete
OMEN by HP 27 inch FHD 240Hz Gaming Monitor - OMEN 27s	780G5AS	obsolete
OMEN by HP 27 inch FHD 240Hz Gaming Monitor - OMEN 27s	780G5E9	obsolete
OMEN by HP 27 inch FHD 240Hz Gaming Monitor - OMEN 27s	780G6AA	
OMEN by HP 27 inch QHD 165Hz Gaming Monitor - OMEN 27q	780H4AA	
OMEN by HP 27 inch QHD 240Hz Gaming Monitor - OMEN 27qs	780J4AA	
OMEN by HP 27 inch UHD 144Hz Gaming Monitor - OMEN 27k	780G8AA	
OMEN by HP 27 inch UHD 144Hz Gaming Monitor - OMEN 27k	780G8AS	
OMEN by HP 27 inch UHD 144Hz Gaming Monitor - OMEN 27k	780G8E9	
OMEN by HP 27 inch UHD 144Hz Gaming Monitor - OMEN 27k	780G9AA	
OMEN by HP 31.5 inch QHD 165Hz Curved Gaming Monitor - OMEN 32c	780K6AA	
OMEN by HP 31.5 inch QHD 165Hz Curved Gaming Monitor - OMEN 32c	780K6AS	
OMEN by HP 31.5 inch QHD 165Hz Curved Gaming Monitor - OMEN 32c	780K6E9	
OMEN by HP 31.5 inch QHD 165Hz Curved Gaming Monitor - OMEN 32c	780K7A6	
OMEN by HP 31.5 inch QHD 165Hz Curved Gaming Monitor - OMEN 32c	780K7AA	
OMEN by HP 31.5 inch QHD 165Hz Gaming Monitor - OMEN 32q	780K0AA	
OMEN by HP 31.5 inch QHD 165Hz Gaming Monitor - OMEN 32q	780K0AS	
OMEN by HP 31.5 inch QHD 165Hz Gaming Monitor - OMEN 32q	780K0E9	
OMEN by HP 31.5 inch QHD 165Hz Gaming Monitor - OMEN 32q	780K1AA	
OMEN by HP 31.5 inch UHD 144Hz Smart Gaming Monitor - OMEN 32x	99Z68AA	
OMEN by HP 31.5 inch UHD 144Hz Smart Gaming Monitor - OMEN 32x	99Z68AS	
OMEN by HP 31.5 inch UHD 144Hz Smart Gaming Monitor - OMEN 32x	99Z68E9	
OMEN by HP 31.5 inch UHD 144Hz Smart Gaming Monitor - OMEN 32x	99Z69AA	
OMEN by HP 34 inch WQHD 165Hz Curved Gaming Monitor - OMEN 34c	780K8AA	

## Disclaimer — Copyright

Intel, Core, Optane, Celeron, Pentium, Iris, XMM, and Thunderbolt are trademarks or registered trademarks of Intel Corporation or its subsidiaries in the United States and other countries. AMD, Ryzen, Athlon, and Radeon are trademarks of Advanced Micro Devices, Inc. Qualcomm and Snapdragon are trademarks or registered trademarks of Qualcomm Technologies, Inc. and/or its subsidiaries. Bluetooth is a trademark owned by its proprietor and used by HP Inc. under license. NVIDIA and GeForce are trademarks and/or registered trademarks of NVIDIA Corporation in the U.S. and other countries. USB Type-C® and USB-C® are registered trademarks of USB Implementers Forum. DisplayPort™ and the DisplayPort™ logo are trademarks owned by the Video Electronics Standards Association (VESA®) in the United States and other countries. McAfee and McAfee LiveSafe are trademarks or registered trademarks of McAfee LLC in the United States and other countries. ENERGY STAR is a registered trademark of the U.S. Environmental Protection Agency. All other trademarks are the property of their respective owners.

© Copyright 2026 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Apr 24, 2026 1:18 PM UTC+0000