



Performance meets ultra-thin, durability[1] for the AI era.

Break through AI workloads while multitasking seamlessly with the lightweight, ultra-thin HP OmniBook Ultra. This premium 14-inch laptop is designed for fast multitasking and AI-powered performance, ideal for those seeking a reliability for business, remote, and hybrid work. Its vivid 3K OLED[4] touchscreen[3] and durable[1] design make it a strong fit for professionals working from anywhere.

Slim enough to go. Strong enough to go further.

Take high performance anywhere with an ultra-thin, ultra-light design crafted from forged aluminum.

Uncompromised performance. Powered by you.

Break through AI workloads with Intel® Core™ Ultra[5] performance and advanced graphics[6] for smooth productivity.

Smarter tools. Sharper you.

Unlock your potential with AI tools like adaptive intelligence, 3K OLED[4], an AI-powered camera[7], and immersive audio.

Featuring

Get a fresh perspective

From a rejuvenated Start menu, to new ways to connect to your favorite people, news, games, and content—Windows 11 is the place to think, express, and create in a natural way. [12]

Intel® Core™ Ultra 9 Series 3 processor

No tradeoffs. Intel® Core™ Ultra Series 3 processors deliver what matters: incredible battery life, powerful performance, and built-in graphics and AI to revolutionize how you create, game, and work anywhere. Feel the power of Intel Inside®. [13]

Intel® Evo™


The Intel® Evo™ platform brings together the perfect combination of performance, responsiveness, battery life and stunning visuals in a new class of laptops. These designs are verified by Intel for an exceptional laptop experience, anywhere. [14]

Intel® Graphics

Stream your favorite shows, hop on video calls, and scroll through photo edits. All with smooth, responsive visuals. Built-in Intel® Graphics handle everyday entertainment and multitasking with ease, no extra GPU, no extra bulk. [15]

3K OLED display

See more of your screen with less scrolling with a 3:2 aspect ratio that delivers an optimized portrait view for a more comfortable way to read and browse. [16]



Specifications

Operating System Software	Windows 11 Pro
Product Color Description (fixed)	Eclipse gray aluminum
Product Design	Sandblasted finish
Processor Family	Intel® Core™ Ultra 9 processor
Processor Name	Intel® Core™ Ultra 9 386H (up to 4.9 GHz with Intel® Turbo Boost Technology, 18 MB L3 cache, 16 cores, 16 threads) [6,7]
Chipset	Intel® integrated SoC
Standard Memory Description 01	32 GB LPDDR5x-9523 MT/s (onboard)
Hard Drive Description (01)	1 TB PCIe® Gen5 NVMe™ M.2 SSD
Graphics Card Segment 01	Integrated
GScardseg 01 Available Card 01	Intel® Graphics
Display Description (metric)	35.6 cm (14") diagonal, 3K (2880 x 1800), OLED, multitouch-enabled, up to 120 Hz, 0.2 ms response time, UWVA, edge-to-edge glass, micro-edge, Corning® Gorilla® Glass 3, Low Blue Light, SDR 500 nits, HDR 1100 nits, 100% DCI-P3
Display Description	14" diagonal, 3K (2880 x 1800), OLED, multitouch-enabled, up to 120 Hz, 0.2 ms response time, UWVA, edge-to-edge glass, micro-edge, Corning® Gorilla® Glass 3, Low Blue Light, SDR 500 nits, HDR 1100 nits, 100% DCI-P3
Screen-To-Body Ratio (without speakers)	91% ^[18]
Audio Features	DTS:X® Ultra; Quad speakers; HP Audio Boost; Poly Studio
Product Dimensions (metric)	31.11 x 21.56 x 1.07 cm
Product Dimensions (imperial)	12.25 x 8.49 x 0.42 in
Weight (metric)	1.27 kg
Weight (imperial)	2.81 lb
Package Dimensions (metric)	6.3 x 45.8 x 28 cm
Package Dimensions (imperial)	2.48 x 18.03 x 11.02 in
Package Weight (metric)	2.24 kg
Package Weight (imperial)	4.94 lb
Keyboard	Full-size, backlit, darker eclipse gray opaque keyboard
Pointing Device	Haptic touchpad
Sensors	Accelerometer; Gyroscope; IR thermal sensor
Camera	5MP IR camera with HDR auto switch, temporal noise reduction and integrated dual array digital microphones
External I/O Ports	1 headphone/microphone combo; 3 Thunderbolt™ 4 with USB Type-C® 40Gbps signaling rate (USB Power Delivery 3.1, DisplayPort™ 2.1, HP Sleep and Charge) ^[19]
Wireless Technologies	Intel® Wi-Fi 7 BE211 (2x2) and Bluetooth® 6.0 wireless card ^[12,46]
Power Supply Type	65 W USB Type-C® GaN power adapter
Battery Type	4-cell, 70 Wh Li-ion polymer (<i>[23]</i>)
Battery Recharge Time	Supports battery fast charge: approximately 50% in 45 minutes ^[5]
Energy Star Certified	ENERGY STAR® certified
Sustainable Impact Specifications	Ocean-bound plastic in speaker enclosure(s) and bezel; Recycled metal in cover, keyboard frame and base; Keyboard keycaps, scissors and keyboard plate contain post-consumer recycled materials
Security Management	Mic mute key; Camera privacy shutter; Trusted Platform Module (Firmware TPM) support
Software Included	McAfee Online Protection 30-day trial
Software - Productivity & Finance	1 month trial for new Microsoft 365 customers ^[24,50]
Cloud Service	100 GB Dropbox storage for 3 months ^[1]
UPC Number	821844259887

Top Recommended Displays, Accessories and Services

No Top Recommended Displays, Accessories and Services

Messaging Footnotes

[1] Testing is not intended to demonstrate fitness of U.S. Department of Defense (DoD) contract requirements or for military use. Test results are not a guarantee of future performance under these test conditions. Accidental damage requires an optional HP Accidental Damage Protection Care Pack.

[3] Display measured diagonally.

[4] All performance specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.

[5] Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance. Intel® Turbo Boost performance varies depending on hardware, software and overall system configuration. See <http://www.intel.com/technology/turboboost/> for more information.

[6] Intel® Arc™ Graphics capabilities require system to be configured with Intel® Core™ Ultra processors with dual channel memory and at least with 16GB (and above) memory. Intel® Arc™ Graphics with Intel® Core™ Ultra processors with single channel memory will only function as Intel® Graphics brand.

[7] Camera resolution refers to the image sensor active pixels. The actual image capture pixels and aspect ratio depend on the app selected.

[12] Not all features are available in all editions or versions of Windows. Systems may require upgraded and/or separately purchased hardware, drivers, software or BIOS update to take full advantage of Windows functionality. Windows is automatically updated and enabled. High speed internet and Microsoft account required. ISP fees may apply and additional requirements may apply over time for updates. See <http://www.windows.com>.

[13] Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering is not a measurement of higher performance.

[14] Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.

[15] For more complete information on configurations and workloads, visit www.Intel.com/PerformanceIndex.

[16] All performance specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary, either higher or lower. Display measured diagonally

Technical Specifications Footnotes

[1] 100 GB of free Dropbox storage for 3 months from date of registration. For complete details and terms of use, including cancellation policies, visit the Dropbox website at <https://www.dropbox.com/help/space/hp-promotion>. Internet service required and not included.

[5] Recharges your battery up to 50% within 45 minutes when the system is off using "shut down" command, using HP adapter provided with the notebook or recommended power adapter disclosed in specifications (see <http://store.hp.com>). After charging has reached 50% capacity, charging speed will return to normal speed. Charging time may vary +/-10% due to System tolerance. Available on select HP products.

[6] Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.

[7] Intel® Turbo Boost performance varies depending on hardware, software and overall system configuration. See <http://www.intel.com/technology/turboboost/> for more information.

[12] Wireless access point and Internet service required and sold separately. Availability of public wireless access points limited. Wi-Fi 7 (802.11BE) functionality requires Windows 11 2024, select Intel® Core™ or Intel® Core™ Ultra processor, and a Wi-Fi 7 router, sold separately. Wi-Fi 7 is backwards compatible with prior 802.11 specs. Available in countries where Wi-Fi 7 is supported. The specification for 802.11BE is a draft specification and is not final. If the final specification differs from the draft specification, it may affect the ability of the device to communicate with other 802.11BE devices.

[18] Percent of active plus nonactive viewing area to active viewing area plus border. Measure with lid vertical to the desk. Calculated to the nearest whole percent may vary +/-0.5%.

[19] For best results with HP Sleep and Charge, use a USB charging protocol standard cable or cable adapter with an external device.

[24] Must activate within 180 days of Windows activation.

[46] Bluetooth® 6.0 operation requires Microsoft OS/Chrome OS support. Until Microsoft OS/Chrome OS support is available, Bluetooth® 6.0 will function as Bluetooth® 5.4 or lower.

© Copyright 2026 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Intel, Core, Optane, Celeron, Pentium, Iris, XMM, and Thunderbolt are trademarks or registered trademarks of Intel Corporation or its subsidiaries in the United States and other countries. AMD, Ryzen, Athlon, and Radeon are trademarks of Advanced Micro Devices, Inc. Qualcomm and Snapdragon are trademarks or registered trademarks of Qualcomm Technologies, Inc. and/or its subsidiaries. Bluetooth is a trademark owned by its proprietor and used by HP Inc. under license. NVIDIA and GeForce are trademarks and/or registered trademarks of NVIDIA Corporation in the U.S. and other countries. USB Type-C® and USB-C® are registered trademarks of USB Implementers Forum. DisplayPort™ and the DisplayPort™ logo are trademarks owned by the Video Electronics Standards Association (VESA®) in the United States and other countries. McAfee and McAfee LiveSafe are trademarks or registered trademarks of McAfee LLC in the United States and other countries. ENERGY STAR is a registered trademark of the U.S. Environmental Protection Agency. All other trademarks are the property of their respective owners.

