

Product data sheet

Specifications



NetShelter SV 42U 600mm Wide x 1060mm Deep Enclosure without Sides Black

AR2401

Overview

Presentation	Universal IT enclosure provided with no side panels for spaces that require less security at the rack or will be paired with other enclosures to form a row and position side panels only at the row ends. The enclosure is for low to medium density server and networking applications. Compact width to optimize data center space. 42U height to easily roll through doorways.
Lead time	Usually in Stock

Main

Product or Component Type	Rack enclosure
Number of rack unit	42U
Provided equipment	Baying hardware Door key Doors Leveling feet Mounting Hardware Pre-installed casters 4 x Bolt down brackets Roof Unpacking sheet

Physical

Height	81.0 in (2057 mm)
Width	23.6 in (600 mm)
Depth	41.7 in (1060 mm)
Net Weight	187.4 lb(US) (85 kg)
Color	Black
Mounting preference	No preference
Mounting Mode	Not rack-mountable
Maximum Mounting Depth	30.6 in (777.2 mm)
Minimum Mounting Depth	6.6 in (167.6 mm)
Rack Width	19"
Marking	15 gauge EIA mounting rail 16 gauge front door 18 gauge post 16 gauge rear door 19 gauge roof 18 gauge side panels
Permanent permissible load	1014 lb(US) (459.9 kg) dynamic 2205 lb(US) (1000.2 kg) static

Conformance

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	UL 2416
	UL 60950-1
	EIA-310E

Ordering and shipping details

GTIN	731304302056
------	--------------

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	85.9 in (218.1 cm)
Package 1 Width	45.7 in (116 cm)
Package 1 Length	27.6 in (70 cm)
Package weight(Lbs)	225.5 lb(US) (102.3 kg)

Contractual warranty

Warranty (in months)	60
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Total lifecycle Carbon footprint	359 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	343 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	9 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	0 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	8 kg CO2 eq.

Use Better



Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Compliant
REACH Regulation	Free of Substances of Very High Concern above the threshold

Use Longer



Lifetime extension

Repair	No
--------	----

Use Again




Repack and remanufacture

Recyclability potential, in %	95
Take-back	Nej

Image of product / Alternate images

Alternative


















Image of product in real life situation

