

# Product data sheet

Specifications



## Power Cord Kit (6 ea), Locking, C13 to C14, 1.2m, North America

AP8704S-NA

### Overview

|              |                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |
|--------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Presentation | Free up space and secure power cords between rack-mount PDUs and attached IT equipment with this exclusive easy-to-use cord retention method. While these cords will fit into any standard IEC receptacle or power inlet; the "locking" feature is enabled only when used with APC AP8000 series Rack PDUs or IT equipment with built-in locking receptacles. These locking connectors reduce the probability of accidentally disconnecting cords and dropping loads. |
| Lead time    | Usually in Stock                                                                                                                                                                                                                                                                                                                                                                                                                                                      |

### Main

|                           |               |
|---------------------------|---------------|
| Product or Component Type | Power cord    |
| Input Connection Type     | IEC 60320 C14 |
| Cable length              | 4 ft (1.2 m)  |
| Number of cables          | 6             |

### Physical

|                     |                       |
|---------------------|-----------------------|
| Color               | Black                 |
| Height              | 9.45 in (24 cm)       |
| Width               | 2.76 in (7 cm)        |
| Depth               | 1.77 in (4.5 cm)      |
| Net Weight          | 2.23 lb(US) (1.01 kg) |
| Mounting preference | No preference         |
| Mounting Mode       | Not rack-mountable    |

### Input

|                      |      |
|----------------------|------|
| Max line current     | 10 A |
| Input current limits | 10 A |

### Output

|                                |                 |
|--------------------------------|-----------------|
| Max current draw               | 10 A            |
| Number of power socket outlets | 1 IEC 60320 C13 |
| Cord Length                    | 4 ft (1.2 m)    |

### Conformance

|                        |                  |
|------------------------|------------------|
| Product Certifications | CSA<br>UL Listed |
|------------------------|------------------|

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Environmental

|                                       |                                                  |
|---------------------------------------|--------------------------------------------------|
| Ambient air temperature for operation | 32...221 °F (0...105 °C)                         |
| Relative Humidity                     | 20...80 %                                        |
| Operating altitude                    | 0...10000 ft                                     |
| Ambient Air Temperature for Storage   | -13...221 °F (-25...105 °C)                      |
| Storage Relative Humidity             | 20...80 %                                        |
| Storage altitude                      | 0...50000 ft (0.0000000000...15240.0000000000 m) |

## Ordering and shipping details

|      |              |
|------|--------------|
| GTIN | 731304294382 |
|------|--------------|

## Packing Units

|                              |                       |
|------------------------------|-----------------------|
| Unit Type of Package 1       | PCE                   |
| Number of Units in Package 1 | 1                     |
| Package 1 Height             | 9.45 in (24 cm)       |
| Package 1 Width              | 1.77 in (4.5 cm)      |
| Package 1 Length             | 2.76 in (7 cm)        |
| Package 1 Weight             | 2.23 lb(US) (1.01 kg) |

## Contractual warranty

|          |                           |
|----------|---------------------------|
| Warranty | 2 years repair or replace |
|----------|---------------------------|

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

| Environmental footprint                        |                                               |
|------------------------------------------------|-----------------------------------------------|
| Carbon footprint (kg CO2 eq, Total Life cycle) | 318                                           |
| Environmental Disclosure                       | <a href="#">Product Environmental Profile</a> |

Use Better

| Materials and Substances          |                                                                                                                                                                                                                                                    |
|-----------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <a href="#">EU RoHS Directive</a> | Compliant                                                                                                                                                                                                                                          |
| REACH Regulation                  | <a href="#">REACH Declaration</a>                                                                                                                                                                                                                  |
| California proposition 65         | WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |

Use Again

| Repack and remanufacture    |                                           |
|-----------------------------|-------------------------------------------|
| Circularity Profile         | <a href="#">End of Life Information</a>   |
| Halogen content performance | Product contains halogen above thresholds |
| Take-back                   | Yes                                       |