

APC Smart-UPS X, Line Interactive, 3kVA, Rack/tower convertible 4U, 208V, 2x NEMA L6-20R+4x IEC C13+2x IEC C19, SmartSlot,Extended runtime,Short depth

SMX3000HVT

Overview

Presentation	Intelligent and efficient network power protection from entry level to scalable runtime. Ideal UPS for servers, point-of-sale, routers, switches, hubs and other network devices.
Lead time	Usually in Stock
Main	
Main Input Voltage	208 V
Other Input Voltage	220 V 230 V 240 V
Main Output Voltage	208 V
Other Output Voltage	220 V 230 V 240 V
Kw Rating	2700 W
Rated power in VA	3000 VA
Product or Component Type	Uninterruptible power supply (UPS)
Input Connection Type	NEMA L6-20P
output connection type	2 NEMA L6-20R 4 IEC 320 C13 3 IEC Jumpers 2 IEC 320 C19
Number of rack unit	4U
Number of cables	1
Battery Type	Lead-Acid battery
Provided equipment	CD with software Documentation CD Smart UPS signalling RS-232 cable User Manual USB cable Rack Mounting brackets
Range of Product	Smart-UPS

Complementary

Communication port type SmartSlot

Batteries & Runtime

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Run Time	View Runtime Graph ☐
Efficiency	View Efficiency Graph ☐
Extendable Run Time	1
Included Battery Modules	0
Battery Slots Empty	0
Typical recharge time	3 h
RBC Quantity	1
Battery life	35 year(s)
Replacement battery	APCRBC143 ☐
Battery Charge Power (Watts)	245 W rated

General

Number of power module	0
Number of power module filled slots	0
Number of power module free slots	0
product web sub-family	Extended run
Redundant	No

Physical

color	Black
Height	17.01 in (43.2 cm)
Width	7.01 in (17.8 cm)
Depth	19.02 in (48.3 cm)
Net Weight	85.19 lb(US) (38.64 kg)
Mounting Location	Front
Mounting preference	Lower
Mounting Mode	Rack-mounted
Two post mountable	1
USB compatible	Yes

Input

Efficiency at full load	141255 V 160280 V
Input Frequency	50/60 Hz +/- 3 Hz auto-sensing

Output

Crest factor	3:1
Harmonic distortion	Less than 5%
Maximum configurable power in VA	3000 VA
Max Configurable Power (Watts)	2700 W
Transfer Time	2-4 ms 4ms typical : 8ms maximum

Topology	Line Interactive
Wave type	Sine wave
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains

Conformance

Product Certifications	C-tick	
	CE	
	CSA	
	GOST	
	IRAM	
	VDE	

Environmental

Acoustic level	55 dBA
Online Thermal Dissipation	184 Btu/h
Operating altitude	010000 ft
Ambient air temperature for operation	32104 °F (040 °C)
Ambient Air Temperature for Storage	5113 °F (-1545 °C)
Storage altitude	050000 ft (0.000000000015240.0000000000 m)
Relative Humidity	095 %
Storage Relative Humidity	095 %

Communications & Management

control panel	Multi-function LCD status and control console
Emergency Power Off (EPO)	Yes
Free slots	1
Control panel	LED status display with on line : on battery : replace battery and overload indicators
Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays

Surge Protection and Filtering

Surge energy rating	645 J
Filtering	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : m

Ordering and shipping details

GTIN	731304292630
Country of origin	PH

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	12.99 in (33 cm)
Package 1 Width	24.92 in (63.3 cm)
Package 1 Length	23.07 in (58.6 cm)
Package 1 Weight	105.23 lb(US) (47.73 kg)

Pallet unit layers	2		
Pallet layers	4		

Contractual warranty

Warranty

3 years repair or replace (excluding battery) and 2 years for battery, optional on-site warranties available, optional extended warranties available



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

⊘ Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	2792
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
₩ Energy efficiency	
Optimized Energy Efficiency	Energy efficient product

Use Again

○ Repack and remanufacture		
Circularity Profile	End of Life Information	
Removable battery	User replaceable	
Take-back	Yes	