

# Product datasheet

Specifications



Easy Rack PDU, Metered Outlet,  
0U, 3 Phase, 11kW, 230V, 16A,  
(18) C13 and (6) C19 outlets,  
IEC60309 3P+N+PE inlet

EPDU2216MBO

## Overview

|           |                  |
|-----------|------------------|
| Lead Time | Usually in Stock |
|-----------|------------------|

## Main

|                           |                    |
|---------------------------|--------------------|
| Colour                    | Black              |
| Product Or Component Type | PDU                |
| Pdu Type                  | Metered outlet     |
| Cord Length               | 3 m                |
| Number Of Cables          | 1                  |
| Provided Equipment        | Installation guide |

## Complementary

|                             |                            |
|-----------------------------|----------------------------|
| Input Voltage               | 400 V 3 phases             |
| Height                      | 1800 mm                    |
| Width                       | 55 mm                      |
| Output Voltage              | 230 V                      |
| Depth                       | 56 mm                      |
| Net Weight                  | 6.82 kg                    |
| Mounting Location           | Side                       |
| Mounting Preference         | No preference              |
| Input Plug Type             | IEC 60309 16 A 3P + N + PE |
| Mounting Mode               | Not rack-mountable         |
| Rack Units                  | 0U                         |
| Usb Compatible              | No                         |
| Mounting Position           | Vertical                   |
| Communication Port Protocol | SNMP                       |
| [In] Rated Current          | 16 A                       |
| Max Line Current            | 16 A                       |
| Input Current Limits        | 16 A                       |
| Load Capacity               | 11000 VA                   |
| Network Frequency           | 50/60 Hz                   |
| Plug Standard               | IEC 60309                  |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                            |                       |
|----------------------------|-----------------------|
| Outlet Type And Quantity   | 18 IEC 60320 C13 10 A |
| Communication Network Type | 10/100BASE-T          |

## Environment

|                                       |             |
|---------------------------------------|-------------|
| Product Certifications                | CE          |
| Ambient Air Temperature For Operation | -5...50 °C  |
| Relative Humidity                     | 5...95 %    |
| Operating Altitude                    | 0...3000 m  |
| Ambient Air Temperature For Storage   | -25...65 °C |
| Storage Relative Humidity             | 5...95 %    |
| Storage Altitude                      | 0...15000 m |

## Packing Units

|                              |         |
|------------------------------|---------|
| Unit Type Of Package 1       | PCE     |
| Number Of Units In Package 1 | 1       |
| Package 1 Height             | 203 cm  |
| Package 1 Width              | 19.5 cm |
| Package 1 Length             | 13 cm   |
| Package 1 Weight             | 7.99 kg |

## Contractual warranty

|          |                            |
|----------|----------------------------|
| Warranty | 2 Years repair and Replace |
|----------|----------------------------|

Sustainability



**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)  
[Guide to assess a product’s sustainability >](#)



RoHS/REACH

Well-being performance

 Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Compliant with Exemptions