

## SPOS G86-61400



Models may vary from the image shown

### Freely Programmable USB Keyboard With Flexible Layout and a Dust and Water Resistant Key Field in Accordance With IP54

The height of professionalism in both look and function. The fully programmable keyboard with extended alphanumeric layout and replaceable keys is designed first and foremost for commercial use at the POS. The model is extremely slim with its compact design and can also be inserted in recesses in the table.

### Key Benefits

- Full Alphanumeric Layout incl. Numeric Keypad
- Compact - only 360 mm width
- User-friendly unstinted standard 19 mm key spacing
- IP54 rated spill and dust resistant key section
- Flexible layout customization with relegendable keys
- Fully programmable USB 2.0 keyboard
- Comprehensive UPOS support
- Integrated memory
- Cut-out mounting capabilities (circumferential rim)
- Pluggable feet

### Technical Data:

#### Layout (country or language):

(possible country/layout versions, others available on request)  
US English with EURO symbol

#### Housing Color:

Product dependant, see table "Models"

#### Key Color:

Product dependant, see table "Models"

#### Weight (product):

approx. 1400 g / 3.09 lb

#### Total Weight (with packaging):

approx. 1600 g / approx. 3.53 lb

#### Cable Length:

approx. 1.85 m / approx. 6.07 ft

#### Storage Temperature:

-20°C to 60°C / -4° F to 140° F

#### Operating Temperature:

0°C to 50°C / 32° F to 122° F

#### Current Consumption:

max. 100 mA

#### Interface:

- USB

#### Product Approvals:

- cURus 
- CE 
- FCC 
- RCM 

#### System Requirements:

- USB plug and USB supporting operating system

#### Box Contents:

- SPOS G86-61400
- Printed instructions
- CD-ROM with up-to-date software
- Keycap puller
- 2 Plug-in feet

#### Dimensions (product):

approx. 360 x 198 x 38 mm / approx. 14.17 x 7.80 x 1.50 in

#### Packaging Dimensions:

approx. 415 x 260 x 50 mm / approx. 16.33 x 10.24 x 1.97 in

#### Reliability:

- Standard keys (1x1): >25 mill. operations
- Multiple keys (1x2, 2x1, 2x2): >20 mill. operations

#### Keyboard:

- Protection Class: IP54
- Service life, standard key: > 25 million key operations
- Inscription Technology: Laser
- Number of Keys: 135
- Number of Programmable Keys: 135
- Number of Relegendable Keys: 54

#### Packaging Unit:

- Number of products in the master package: 15
- Number of master packages per pallet: 8

#### Warranty:

3-year limited manufacturer's guarantee  
For the first two years after delivery, the statutory warranty applies. In the third year after delivery, CHERRY voluntarily grants an additional warranty according to the following conditions ("extended warranty"). In the event of a defect, please contact the seller of your CHERRY product. Do not carry out any repairs on your own and do not open the product. There is no warranty if unauthorized changes to the product cause a defect.

Conditions for the extended warranty:

In the case of a defect after the first 2 years after delivery of

the CHERRY product, CHERRY grants its customers for the additional period of one year the right to assert claims for cure, i.e. demand that the defect is remedied or a thing free of defects is supplied. The extended warranty is to be asserted against the seller of the CHERRY product upon presentation of the original invoice, proof of purchase or a comparable proof of the time of purchase.

CHERRY, and the seller of the CHERRY product, where applicable, shall remedy the defect in the event the customer has justified claims for cure under the terms of the extended warranty.

Excluded from the extended warranty are damages caused by improper use, in particular by the effects of chemical substances, other damages caused by external influences, as well as normal wear and tear and optical changes, in particular discoloration or abrasion of shiny areas. Also excluded from the extended warranty are accessories and other parts which are not an integral part of the purchased item.

Errors, technical changes and delivery delays may occur. Technical information refers only to the specifications of the products. Features may differ from the information provided.

**Models:**

(possible country/layout versions, others available on request)

	<b>Product Name</b>	<b>Order Number</b>	<b>Housing Color</b>	<b>Key Color</b>
1	SPOS G86-61400	G86-61400EUADAA	black	black
2	SPOS G86-61400	G86-61400EUAEAA	light grey	light grey