



APC NetShelter Basic Rack PDU, Zero U, 32A, 230V, 20 C13 and 4 C19 outlet, IEC309 inlet

AP7553

Overview

Lead time Usually in Stock

Main

Colour	Black	
Product or component type	PDU	
PDU type	Basic	
Cord length	3 m	
Number of cables	1	
Provided equipment	Installation guide Rack mounting brackets Toolless mounting kit	

Complementary

Input Voltage	200 V	
	208 V	
	230 V	
Height	1619 mm	
Width	56 mm	
Output Voltage	230 V	
Depth	44 mm	
Net weight	5.57 kg	
Mounting location	Side	
Mounting preference	No preference	
Input Plug Type	IEC 60309 32 A 2P + E	
Mounting mode	Rack-mounted	
Rack units	0U	
Mounting position	Vertical	
Input current limits	32 A	
Load capacity	7400 VA	
Network frequency	4763 Hz	
Outlet type and quantity	20 IEC 60320 C13	
	4 IEC 60320 C19	

Environment

Product certifications	CE VDE
Ambient air temperature for operation	045 °C
Relative humidity	095 %
Operating altitude	010000 ft
Ambient air temperature for storage	-2565 °C
Storage Relative Humidity	095 %
Storage altitude	015240 m

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	12.000 cm
Package 1 Width	15.000 cm
Package 1 Length	212.000 cm
Package 1 Weight	8.943 kg
Unit Type of Package 2	PAL
Number of Units in Package 2	10
Package 2 Height	75.000 cm
Package 2 Width	120.000 cm
Package 2 Length	222.000 cm
Package 2 Weight	101.700 kg

Contractual warranty

Warranty (in months)



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

⊘ Environmental footprint	
Total lifecycle Carbon footprint	4476
Environmental Disclosure	Product Environmental Profile

Use Better

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant with Exemptions
SCIP Number	1cdb2fed-a06f-4574-913d-8df8e70936b2
REACh Regulation	REACh Declaration
Halogen-free status	Product contains halogen above thresholds
☼ Energy efficiency	
Energy Efficiency Optimized	Energy efficient product

Use Again

○ Repack and remanufacture	
End of life manual availability	End of Life Information
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Image of product / Alternate images

Alternative

