

APC Smart-UPS On-Line, 6kVA/6kW, Rackmount 4U, 208V, 2x L6-20R+3x L6-30R NEMA outlets, Network Card+SmartSlot, Extended runtime, W/ rail kit [TAA]

SRT6KRMXLT

Usually in Stock

Product availability: Stock - Normally stocked in distribution facility

#### Overview

Lead time

Main
Main Input Voltage 208 V

**Product or Component Type** Uninterruptible power supply (UPS) Other Input Voltage 240 V Main Output Voltage 208 V Other Output Voltage 240 V Kw Rating 6000 W Rated power in VA 6000 VA output connection type 2 NEMA L6-20R 3 NEMA L6-30R Output connector type Hard Wire 3-wire (2PH + G) 1 Number of rack unit 4U Provided equipment CD with software Documentation CD Installation guide Rack mounting hardware Rack Mounting brackets

Rack Mounting brackets
Rack Mounting support rails
Temperature Probe
USB cable

Warranty card
Web/SNMP Management Card

Range of Product Smart-UPS On-Line

#### **Batteries & Runtime**

Run Time	View Runtime Graph ☐	
Efficiency	View Efficiency Graph ☐	
Battery Type	Lead-Acid battery	
Battery Voltage	192V	
Extendable Run Time	1	
Included Battery Modules	0	
Battery Slots Empty	0	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Typical recharge time	1.5 h
RBC Quantity	1
Battery life	35 year(s)
Replacement battery	APCRBC140 ☐
Battery Charge Power (Watts)	579 W rated

### General

Number of power module filled slots	0	
Number of power module free slots	0	
product web sub-family	High density	
Redundant	No	
Topology	Double Conversion Online	

# **Physical**

<b>,</b>		
color	Black	
Height	6.85 in (17.4 cm)	
Width	17.01 in (43.2 cm)	
Depth	28.31 in (71.9 cm)	
Net Weight	134.99 lb(US) (61.23 kg)	
Mounting Location	Front	
Mounting preference	Lower	
Mounting Mode	Rack-mounted	
Two post mountable	0	
USB compatible	Yes	
Mounting position	Horizontal	

# Input

Efficiency at full load	100275 V adjustable (half load)	
Number of input connectors	1 Hard Wire 3-wire (2PH + G)	
Input Frequency	40 - 70 Hz auto-sensing	

# Output

Bypass type	Internal Bypass (Automatic and Manual)	
Crest factor	3:1	
Harmonic distortion	Less than 2%	
Maximum configurable power in VA	6000 VA	
Max Configurable Power (Watts)	6000 W	
Wave type	Sine wave	
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains	

# Conformance

Product Certifications ENERGY STAR V2.0 (USA)
FCC part 15 class A
NOM

NOM UL 1778

#### **Environmental**

Acoustic level	55 dBA	
Online Thermal Dissipation	1402 Btu/h	
Operating altitude	010000 ft	
Ambient air temperature for operation	32104 °F (040 °C)	
Ambient Air Temperature for Storage	5113 °F (-1545 °C)	
Storage altitude	050000 ft (0.000000000015240.0000000000 m)	
IP degree of protection	IP20	
Relative Humidity	095 % non-condensing	
Storage Relative Humidity	095 % non-condensing	

### **Communications & Management**

Emergency Power Off (EPO)	Yes	
Free slots	1	
Pre-Installed SmartSlot™ Cards	Network management card 3 with environmental monitoring	
Alarm	Audible and visible alarms : prioritized by severity	

### **Surge Protection and Filtering**

Surge energy rating 480

# Ordering and shipping details

Category	11309-APC RESALE PRODUCTS	
Discount Schedule	APC1	
GTIN	731304308522	
Returnability	No	
Country of origin	PH	

# **Packing Units**

Unit Type of Package 1	PCE	
Number of Units in Package 1	1	
Package 1 Height	14.57 in (37 cm)	
Package 1 Width	37.80 in (96 cm)	
Package 1 Length	24.02 in (61 cm)	
Package 1 Weight	150.003 lb(US) (68.04 kg)	

### **Contractual warranty**

Warranty 3 years repair or replace (excluding battery) and 2 years for battery



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

#### Environmental Data explained >

How we assess product sustainability >

∇ Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	13567
Environmental Disclosure	Product Environmental Profile

#### **Use Better**

Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
China RoHS Regulation	China RoHS declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
Optimized Energy Efficiency	Energy efficient product
ENERGY STAR®	ENERGY STAR UPS V2.0 (USA)

#### **Use Again**

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Removable battery	User replaceable
Take-back	Yes