

# Product data sheet

Specifications



## Interface ports, Management Options, UPS Interface Expander 2, additional UPS interface ports with serial shutdown support

AP9624

### Overview

<b>Presentation</b>	UPS Management SmartSlot offer with serial shutdown support of up to two additional devices such as Servers and Network Storage Devices.
<b>Lead time</b>	Usually in Stock

### Main

<b>Range of Product</b>	Management Options and Cables
<b>Provided Equipment</b>	RS-232 configuration cable User Manual Warranty card
<b>Product or Component Type</b>	Expansion unit
<b>Number of cables</b>	2

### General

<b>Power supply type</b>	Self powered via SmartSlot
--------------------------	----------------------------

### Physical

<b>Net Weight</b>	0.90 lb(US) (0.41 kg)
<b>Width</b>	0.541 ft (0.165 m)
<b>Height</b>	2.008 in (5.1 cm)
<b>Depth</b>	4.5 in (11.4 cm)
<b>Mounting preference</b>	No preference

### Conformance

<b>Standards</b>	EN 55022 Class A EN 55024 FCC Part 15 class A IEC 62040-2 EN 61000-6-1 EN 61000-6-2 EN 55011 EN 55022
<b>Product Certifications</b>	C-tick CE Industry Canada VCCI

### Environmental

<b>Storage Relative Humidity</b>	0...95 %
<b>Relative Humidity</b>	0...95 %

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

<b>Ambient Air Temperature for Storage</b>	5...113 °F (-15...45 °C)
<b>Ambient Air Temperature for Operation</b>	32...104 °F (0...40 °C)
<b>Storage altitude</b>	0...50000 ft (0...15240 m)
<b>Operating altitude</b>	0...10000 ft 0...50000 ft

## Ordering and shipping details

<b>GTIN</b>	731304314974
-------------	--------------

## Packing Units

<b>Unit Type of Package 1</b>	PCE
<b>Nbr. of units in pkg.</b>	1
<b>Package 1 Height</b>	2.008 in (5.1 cm)
<b>Package 1 Width</b>	6.5 in (16.5 cm)
<b>Package 1 Length</b>	9.3 in (23.5 cm)
<b>Package weight(Lbs)</b>	0.90 lb(US) (0.41 kg)

## Contractual warranty

<b>Warranty (in months)</b>	24
-----------------------------	----



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



### Environmental footprint

Total lifecycle Carbon footprint	3 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	0 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	0 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	1 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	0 kg CO2 eq.
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Use Better



### Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
SCIP Number	1cdb2fed-a06f-4574-913d-8df8e70936b2
EU RoHS Directive	<a href="#">Compliant By Exemption</a>
REACH Regulation	<a href="#">Free of Substances of Very High Concern above the threshold</a>
Halogen content performance	Product contains halogen above thresholds

## Use Longer



### Lifetime extension

Repair	No
--------	----

## Use Again



### Repack and remanufacture

Recyclability potential, in %	45
Circularity Profile	<a href="#">End of Life Information</a>
Take-back	Nej
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.