

Product data sheet

Specifications

Rack PDU,Basic, 1U, 16A, 208&230V, (10)C13 & (2)C19



AP9559

Overview

Lead time	Usually in Stock
-----------	------------------

Main

Color	Black
Product or Component Type	PDU
PDU Type	Basic
Cord length	8.2 ft (2.5 m)
Number of cables	1
Provided Equipment	User Manual Rack Mounting brackets

Complementary

Input Voltage	120 V 208 V 230 V
Height	1.73 in (4.4 cm)
Width	17.60 in (44.7 cm)
Output Voltage	120 V 208 V 230 V
Depth	2.24 in (5.7 cm)
Net Weight	2.16 lb(US) (0.98 kg)
Mounting Location	Front Rear
Mounting preference	No preference
Input Plug Type	IEC 60320 C20
Mounting Mode	Rack-mounted
Rack units	1U
Mounting position	Horizontal
Permissible voltage	90...250 V
Max line current	16 A
Input current limits	16 A
Load Capacity	3680 VA
Input Frequency	50/60 Hz

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Outlet type and quantity	10 IEC 60320 C13
	2 IEC 60320 C19

Environment

Product Certifications	cUL Listed
	CE
	UL Listed
	VDE
	Victoria
Ambient air temperature for operation	32...113 °F (0...45 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.0000000000...15240.0000000000 m)

Ordering and shipping details

GTIN	731304123521
------	--------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.50 in (16.5 cm)
Package 1 Width	19.02 in (48.3 cm)
Package 1 Length	5.98 in (15.2 cm)
Package 1 Weight	5.192 lb(US) (2.355 kg)

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	29
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
EU RoHS Directive	Compliant
REACH Regulation	REACH Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov

Energy efficiency	
Optimized Energy Efficiency	Energy efficient product

Use Again

Repack and remanufacture	
Circularity Profile	End of Life Information
WEEE	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Halogen content performance	Product contains halogen above thresholds
Take-back	Yes