

Product data sheet

Specifications



APC Smart-UPS On-Line, 10kVA/10kW, Tower, 208V, 6x C13+4x C19 IEC outlets, Network Card+SmartSlot, Extended runtime, W/O rail kit

SRT10KXLT-IEC

Overview

Lead time	Usually in Stock
-----------	------------------

Main

Main Input Voltage	208 V AC 1 phase 240 V AC 1 phase
Other Input Voltages	240 V
Efficiency at full load	100...275 V adjustable (half load)
Number of input connectors	1 Hard Wire 3-wire (2PH + G)
Input Frequency	40 - 70 Hz auto-sensing
Output voltage	208 V 1 phase 240 V 1 phase
Other Output Voltages	240 V
Rated power in W	10000 W
rated power in VA	10000 VA
output connection type	6 IEC 60320 C13 3 IEC Jumpers 4 IEC 60320 C19
Output connector type	Hard Wire 3-wire (2PH + G) for 1 zone(s)
Bypass type	Internal Bypass (Automatic and Manual)
Crest factor	3 : 1
Harmonic distortion	Less than 2%
Maximum configurable power in VA	10000 VA
Max Configurable Power (Watts)	10000 W
Topology	On-Line
Waveform Type	Sine wave
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains

Complementary

Battery Size	Lead-acid internal included
Emergency Power Off (EPO)	Yes
Free slots	1
Pre-Installed SmartSlot™ Cards	Network management card 3 with environmental monitoring
Alarm	Audible and visible alarms : prioritized by severity

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

UPS connectivity	Serial port USB port Embedded network management card 3 Available expansion slot
Surge energy rating	480 J
color	Black
Height	17.008 in (432 mm)
Width	10.4 in (263 mm)
Depth	28.1 in (715 mm)
Net Weight	245.99 lb(US) (111.58 kg)
Mounting Location	Front
Mounting preference	No preference
Mounting Mode	Rack-mounted with kit
Two post mountable	0
USB compatible	Yes
Mounting mode	Tower with included kit
Provided equipment	CD with software Documentation CD Installation guide Temperature Probe USB cable Warranty card Web/SNMP Management Card
Number of power module filled slots	0
Number of power module free slots	0
Additional specification	High density
Redundant	No
Range of Product	Smart-UPS On-Line
Product or Component Type	Uninterruptible power supply (UPS)

Environment

Product Certifications	ENERGY STAR V2.0 (USA) FCC part 15 class A UL 1778
Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage altitude	0...50000 ft (0...15240 m)
IP degree of protection	IP20
Relative Humidity	0...95 % non-condensing
Storage Relative Humidity	0...95 % non-condensing
Acoustic level	55 dBA
Online Thermal Dissipation	2490 Btu/h
Operating altitude	0...10000 ft

Batteries & Runtime

Run Time [View Runtime Graph](#) 

Efficiency	View Efficiency Graph 
Battery Type	Lead-Acid battery
Battery Voltage	+/-192 V (split battery referenced to neutral)
Extendable Run Time	1
Included Battery Modules	0
Typical recharge time	1.5 h
RBC Quantity	2
Battery Life	3...5 year(s)
Replacement battery	APCRBC140  SRT192BP2US  SRT192RMBPUS 
Battery Charge Power (Watts)	1191 W rated

Ordering and shipping details

GTIN	731304304289
------	--------------

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	18.1 in (46.1 cm)
Package 1 Width	39.4 in (100 cm)
Package 1 Length	23.6 in (60 cm)
Package weight(Lbs)	279.00 lb(US) (126.55 kg)

Contractual warranty

Warranty (in months)	24 Battery 36 UPS
----------------------	-------------------



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Total lifecycle Carbon footprint	20 656 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	1 612 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	18 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	19 011 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	16 kg CO2 eq.
Environmental Disclosure	Product Environmental Profile

Use Better



Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
SCIP Number	409c68a1-39a6-4e5f-b080-12befe783ad8
EU RoHS Directive	Compliant By Exemption
REACH Regulation	Reference contains Substances of Very High Concern above the threshold
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov



Energy efficiency

ENERGY STAR®	ENERGY STAR UPS V2.0 (USA)
--------------	----------------------------

Use Longer



Lifetime extension

Repair	No
--------	----

Use Again



Repack and remanufacture

Recyclability potential, in %	65
Circularity Profile	End of Life Information
Removable battery	User replaceable

Take-back	Yes
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Image of product / Alternate images

Alternative



