

Product data sheet

Specifications



APC Smart-UPS On-Line, 8kVA/
8kW, Tower, 208V, 6x C13+4x C19
IEC outlets, Network
Card+SmartSlot, Extended runtime,
W/O rail kit

SRT8KXLT-IEC

Overview

Lead time	Usually in Stock
-----------	------------------

Main

Main Input Voltage	208 V
Product or Component Type	Uninterruptible power supply (UPS)
Other Input Voltage	240 V
Main Output Voltage	208 V
Other Output Voltage	240 V
Kw Rating	8000 W
Rated power in VA	8000 VA
output connection type	6 IEC 60320 C13 3 IEC Jumpers 4 IEC 60320 C19
Output connector type	Hard Wire 3-wire (2PH + G) 1
Provided equipment	CD with software Documentation CD Installation guide Temperature Probe USB cable Warranty card Web/SNMP Management Card
Range of Product	Smart-UPS On-Line

Batteries & Runtime

Run Time	View Runtime Graph
Efficiency	View Efficiency Graph
Battery Type	Lead-Acid battery
Battery Voltage	+/-192 V (split battery referenced to neutral)
Extendable Run Time	1
Included Battery Modules	0
Typical recharge time	1.5 h
RBC Quantity	2
Battery life	3...5 year(s)
Replacement battery	APCRBC140

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Battery Charge Power (Watts)	1136 W rated
------------------------------	--------------

General

Number of power module filled slots	0
Number of power module free slots	0
product web sub-family	High density
Redundant	No
Topology	Double Conversion Online

Physical

color	Black
Height	17.01 in (43.2 cm)
Width	10.35 in (26.3 cm)
Depth	28.15 in (71.5 cm)
Net Weight	245.99 lb(US) (111.58 kg)
Mounting Location	Front
Mounting preference	No preference
Mounting Mode	Rack-mounted with kit
Two post mountable	0
USB compatible	Yes

Input

Efficiency at full load	100...275 V adjustable (half load)
Number of input connectors	1 Hard Wire 3-wire (2PH + G)
Input Frequency	40 - 70 Hz auto-sensing

Output

Bypass type	Internal Bypass (Automatic and Manual)
Crest factor	3 : 1
Harmonic distortion	Less than 2%
Maximum configurable power in VA	8000 VA
Max Configurable Power (Watts)	8000 W
Wave type	Sine wave
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains

Conformance

Product Certifications	ENERGY STAR V2.0 (USA) FCC part 15 class A UL 1778
------------------------	--

Environmental

Acoustic level	55 dBA
Online Thermal Dissipation	1712 Btu/h

Operating altitude	0...10000 ft
Ambient air temperature for operation	32...104 °F (0...40 °C)
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage altitude	0...50000 ft (0.0000000000...15240.0000000000 m)
IP degree of protection	IP20
Relative Humidity	0...95 % non-condensing
Storage Relative Humidity	0...95 % non-condensing

Communications & Management

Emergency Power Off (EPO)	Yes
Free slots	1
Pre-Installed SmartSlot™ Cards	Network management card 3 with environmental monitoring
Alarm	Audible and visible alarms : prioritized by severity

Surge Protection and Filtering

Surge energy rating	480 J
---------------------	-------

Ordering and shipping details

GTIN	731304313106
------	--------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	18.15 in (46.1 cm)
Package 1 Width	39.37 in (100 cm)
Package 1 Length	23.62 in (60 cm)
Package 1 Weight	279.00 lb(US) (126.55 kg)

Contractual warranty

Warranty	3 years repair or replace (excluding battery) and 2 years for battery
----------	---

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	18644
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant with Exemptions
SCIP Number	409c68a1-39a6-4e5f-b080-12befe783ad8
REACH Regulation	REACH Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Energy efficiency	
Optimized Energy Efficiency	Energy efficient product
 ENERGY STAR®	ENERGY STAR UPS V2.0 (USA)

Use Again

Repack and remanufacture	
Circularity Profile	End of Life Information
Removable battery	User replaceable
WEEE	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Take-back	Yes