

Product data sheet

Specifications



NetShelter SX 48U 600mm Wide Perforated Split Doors Black

AR7107

Overview

Lead time	Usually in Stock
-----------	------------------

Main

Product or Component Type	Door
Provided equipment	Door handle Door mounting hardware Installation guide Key(s)

Physical

Color	Black
Height	85.9 in (2182 mm)
Width	23.6 in (600 mm)
Depth	1.4 in (35 mm)
Net Weight	23.55 lb(US) (10.68 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable
Marking	16 gauge rear door

Ordering and shipping details

GTIN	731304226475
------	--------------

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	8.0 in (20.3 cm)
Package 1 Width	89.02 in (226.1 cm)
Package 1 Length	15.0 in (38.1 cm)
Package weight(Lbs)	39.7 lb(US) (18 kg)

Contractual warranty

Warranty (in months)	24
----------------------	----

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Total lifecycle Carbon footprint	63 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	60 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	2 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	0 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	1 kg CO2 eq.

Use Better



Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Compliant
REACH Regulation	Free of Substances of Very High Concern above the threshold

Use Longer



Lifetime extension

Repair	No
--------	----

Use Again



Repack and remanufacture

Recyclability potential, in %	95
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Image of product / Alternate images

Alternative

