

Rack PDU, Basic, Zero U, 14.4kW, 208V, (24) C13, (4) C19, (2) L6-30R; 3 Cord

AP7569

Overview

Presentation	Basic Rack PDU 14.4 kW solution for high density installations
Lead time	Usually in Stock

Main

Color	Black	
Product or Component Type	PDU	
PDU Type	Basic	
Cord length	3 ft (0.9 m)	
Number of cables	1	
Provided Equipment Cord retention bracket(s) Documentation CD Installation guide Rack Mounting brackets Toolless Mounting Kit		

Complementary

Input Voltage	208 V 3 phase	
Height	70.00 in (177.8 cm)	
Width	2.20 in (5.6 cm)	
Output Voltage	208 V 3 phase	
Depth	3.74 in (9.5 cm)	
Net Weight	16.14 lb(US) (7.32 kg)	
Mounting Location	Side	
Mounting preference	No preference	
Mounting Mode	Rack-mounted	
Rack units	OU	
Mounting position	Vertical	
Line Rated Current	40 A	
Input current limits	50 A	
Load Capacity	14400 VA	
Input Frequency	50/60 Hz	
Number of input connectors	1 CS8365	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Outlet type and quantity	2 NEMA L6-30R	
	24 IEC 60320 C13	
	4 IEC 60320 C19	

Environment

Product Certifications	cUL Listed CSA METI Denan UL Listed	
Standards	UL 60950	
Ambient air temperature for operation	23113 °F (-545 °C)	
Relative Humidity	595 %	
Operating altitude	010000 ft	
Ambient Air Temperature for Storage	-13149 °F (-2565 °C)	
Storage Relative Humidity	595 %	
Storage altitude	050000 ft (0.000000000015240.0000000000 m)	

Ordering and shipping details

GTIN 731304240754

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	80.98 in (205.7 cm)
Package 1 Width	12.24 in (31.1 cm)
Package 1 Length	3.11 in (7.9 cm)
Package 1 Weight	24.87 lb(US) (11.28 kg)

Contractual warranty

Warranty 2 years repair or replace



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	191
Environmental Disclosure	Product Environmental Profile

Use Better

EU RoHS Directive	Compliant
REACh Regulation	REACh Declaration
₩ Energy efficiency	
Optimized Energy Efficiency	Energy efficient product

Use Again

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Halogen content performance	Product contains halogen above thresholds
Take-back	Yes