

Product data sheet

Specifications



APC NetShelter Basic Rack PDU, Zero U, 14.4kW, 208V,24 C13, 4 C19, 2 NEMA L6-30R outlet, 10ft input cord

AP7599

Overview

Presentation	Basic Rack PDU 14.4 kW solution for high density installations
Lead time	Usually in Stock

Main

Color	Black
Product or Component Type	PDU
PDU Type	Basic
Cord length	9.8 ft (3 m)
Number of cables	1
Provided Equipment	Cord retention bracket(s) Documentation CD Installation guide Rack Mounting brackets Toolless Mounting Kit

Complementary

Input Voltage	208 V 3 phase
Height	70 in (1778 mm)
Width	2.2 in (56 mm)
Output Voltage	208 V
Depth	3.7 in (95 mm)
Net Weight	21.74 lb(US) (9.86 kg)
Mounting Location	Side
Mounting preference	No preference
Mounting Mode	Rack-mounted
Rack units	0U
Mounting position	Vertical
Line Rated Current	40 A
Input current limits	50 A
Load Capacity	14400 VA
Input Frequency	50/60 Hz
Number of input connectors	1 CS8365
Outlet type and quantity	2 NEMA L6-30R 24 IEC 60320 C13 4 IEC 60320 C19

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Product Certifications	cUL Listed CSA METI Denan UL Listed
Standards	UL 60950
Ambient Air Temperature for Operation	23...113 °F (-5...45 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 ft (0...15240 m)

Ordering and shipping details

GTIN	731304240761
------	--------------

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	81.0 in (205.7 cm)
Package 1 Width	12.2 in (31.1 cm)
Package 1 Length	3.1 in (7.9 cm)
Package weight(Lbs)	30.47 lb(US) (13.82 kg)

Contractual warranty

Warranty (in months)	24
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Total lifecycle Carbon footprint	241 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	43 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	0.7 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	9 540 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	1 kg CO2 eq.
Environmental Disclosure	Product Environmental Profile

Use Better



Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant
REACH Regulation	Free of Substances of Very High Concern above the threshold
Halogen content performance	Product contains halogen above thresholds

Use Longer



Lifetime extension

Repair	No
--------	----

Use Again



Repack and remanufacture

Recyclability potential, in %	45
Circularity Profile	End of Life Information
Take-back	Nej
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Image of product / Alternate images

Alternative



