# Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# APC 208V/120V 10KVA Step down Transformer



APTF10KT01

### **Overview**

Lead time Special Order - Call for Quoted Lead Times

### Main

Main Input Voltage	208 V	
Product or Component Type	Accessory	
Main Output Voltage	120 V 208 V 240 V	
Output connector type	Hard Wire 3-wire (2PH + G) 1 Hard Wire 4-wire (2PH+N+G) 1	
Number of rack unit	4U	
Provided Equipment	Documentation CD Hardwire panel Installation guide Rack Mounting brackets User Manual	

# **Physical**

Color	Black	
Height	6.89 in (17.5 cm)	
Width	17.01 in (43.2 cm)	
Depth	29.49 in (74.9 cm)	
Net Weight	220.5 lb(US) (100 kg)	
Mounting Location	Front	
Mounting preference	Lower	
Mounting Mode	Rack-mounted with kit	

### Input

Permissible voltage	200240 V
Max line current	60 A
Input current limits	60 A
Load Capacity	10000 VA
Input Frequency	4565 Hz
Number of input connectors	1 Hard Wire 3-wire (2PH + G)

# **Output**

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Max current draw	60 A
Number of power socket outlets	4
Protection Type	Circuit breaker
Efficiency	95 %
Number of power socket outlets	2 NEMA L5-20R 2 NEMA L14-30R

## Conformance

Product Certifications	C-tick	
	CE	
	CSA	
	GOST	
	UL Listed	
	VDE	

### **Environmental**

Ambient air temperature for operation	32104 °F (040 °C)	
Relative Humidity	095 %	
Operating altitude	010000 ft	
Ambient Air Temperature for Storage	-13149 °F (-2565 °C)	
Storage Relative Humidity	095 %	
Storage altitude	050000 ft (0.000000000015240.0000000000 m)	

# Ordering and shipping details

GTIN	731304242215	
O1111	131304242213	

# **Packing Units**

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	15.98 in (40.6 cm)
Package 1 Width	39.37 in (100 cm)
Package 1 Length	23.62 in (60 cm)
Package 1 Weight	275.6 lb(US) (125 kg)

# **Contractual warranty**

Warranty	2 1/2	ars repair or replace



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability

Environmental footprint

Environmental Disclosure Product Environmental Profile

### **Use Better**

EU RoHS Directive Compliant with Exemptions

### **Use Again**

☼ Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	Yes