

Product data sheet

Specifications



APC Universal Transfer Switch 10-Circuit 120/240V

UTS10BI

Overview

Lead time	Usually in Stock
-----------	------------------

Main

Main Input Voltage	120 V 240 V
Product or Component Type	Transfer switch
Main Output Voltage	120 V 240 V
Other Output Voltage	240 V
Input Connection Type	IEC 60320 C14
Number of cables	1
Provided Equipment	Bypass fast-ons Hardwire panel User Manual Installation guide Warranty card

Physical

Color	Black
Height	23.43 in (59.5 cm)
Width	15.51 in (39.4 cm)
Depth	3.31 in (8.4 cm)
Net Weight	27.6 lb(US) (12.5 kg)
Mounting Location	Front Side Top
Mounting preference	No preference
Mounting Mode	Not rack-mountable
USB compatible	No

Input

Input Frequency	47...63 Hz
Max line current	20 A

Conformance

Product Certifications	cTUVus
------------------------	--------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environmental

Ambient air temperature for operation	-13...104 °F (-25...40 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-40...185 °F (-40...85 °C)
Storage altitude	0...50000 ft (0.0000000000...15240.0000000000 m)

Ordering and shipping details

GTIN	731304247463
------	--------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	26.73 in (67.9 cm)
Package 1 Width	8.39 in (21.3 cm)
Package 1 Length	18.70 in (47.5 cm)
Package 1 Weight	29.06 lb(US) (13.18 kg)


Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------


Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)


[How we assess product sustainability >](#)

<div>Environmental footprint</div>	
Environmental Disclosure	Product Environmental Profile

Use Better

<div>Materials and Substances</div>	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant with Exemptions
SCIP Number	0faaa581-e733-4efc-987a-3938986edbd8
REACH Regulation	REACH Declaration
China RoHS Regulation	China RoHS declaration

Use Again

<div>Repack and remanufacture</div>	
Circularity Profile	End of Life Information
Take-back	No