

APC Back-UPS 600VA, 120V, 1 USB charging port, 7 NEMA outlets (2 surge)

BE600M1

Product availability: Stock - Normally stocked in distribution facility

Overview

Lead time Usually in Stock

Main

| Mairi | | |
|---------------------------|------------------------------------|--|
| Main Input Voltage | 120 V | |
| Main Output Voltage | 120 V | |
| Kw Rating | 330 W | |
| Rated power in VA | 600 VA | |
| Product or Component Type | Uninterruptible power supply (UPS) | |
| Input Connection Type | NEMA 5-15P | |
| output connection type | 5 NEMA 5-15R 2 NEMA 5-15R surge | |
| Cable length | 5 ft (1.5 m) | |
| Battery Type | Lead-Acid battery | |
| Provided equipment | User Manual | |
| Range of Product | Back-UPS | |

Batteries & Runtime

| Run Time | View Runtime Graph ☐ | |
|------------------------------|-------------------------|--|
| Efficiency | View Efficiency Graph ☐ | |
| Included Battery Modules | 0 | |
| Battery Slots Empty | 0 | |
| Typical recharge time | 10 h | |
| RBC Quantity | 1 | |
| Battery Voltage | 12 V | |
| Battery Charge Power (Watts) | 7 W rated | |
| Battery power in VAH | 66 VAh runtime | |
| Battery life | 35 year(s) | |
| Replacement battery | APCRBC154 ☐ | |
| Extendable Run Time | 0 | |

General

Number of power module free slots

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| Number of power module filled slots | 0 |
|-------------------------------------|----|
| Redundant | No |

Physical

| color | Black | |
|---------------------|-----------------------|--|
| Height | 5.47 in (13.9 cm) | |
| Width | 10.79 in (27.4 cm) | |
| Depth | 4.13 in (10.5 cm) | |
| Net Weight | 7.69 lb(US) (3.49 kg) | |
| Mounting preference | No preference | |
| Mounting Mode | Not rack-mountable | |
| Two post mountable | 0 | |
| USB compatible | No | |

Input

| Input Frequency | 50/60 Hz +/- 3 Hz auto-sensing | |
|-------------------------|--------------------------------|--|
| Efficiency at full load | 92139 V | |

Output

| Max Configurable Power (Watts) | 330 W | |
|----------------------------------|-------------------------------------|--|
| Output Frequency (sync to mains) | 50/60 Hz +/- 3 Hz sync to mains | |
| Topology | Standby | |
| Wave type | Stepped approximation to a sinewave | |
| Maximum configurable power in VA | 600 VA | |
| Transfer Time | 6ms typical : 10ms maximum | |

Conformance

| Product Certifications | California (CEC) Battery Charger cTUVus NOM |
|------------------------|---|
|------------------------|---|

Environmental

| Ambient air temperature for operation | 32104 °F (040 °C) | |
|---------------------------------------|--|--|
| Relative Humidity | 090 % | |
| Operating altitude | 03000 ft | |
| Ambient Air Temperature for Storage | 5113 °F (-1545 °C) | |
| Storage Relative Humidity | 095 % | |
| Storage altitude | 05000 ft (0.00000000001524.0000000000 m) | |
| Acoustic level | 35 dBA | |
| Online Thermal Dissipation | 16 Btu/h | |

Communications & Management

Control panel LED status display with on line : on battery : replace battery and overload indicators

Alarm when on battery : distinctive low battery alarm : overload continuous tone

Surge Protection and Filtering

| | <u> </u> | |
|----------------------------|---|--|
| Surge energy rating | 490 J | |
| Filtering | Full time multi-pole noise filtering: 0.3% IEEE surge let-through: zero clamping response time: m | |
| Let Through Voltage Rating | 5 V | |

Ordering and shipping details

| Category | 11309-APC RESALE PRODUCTS | |
|-------------------|---------------------------|--|
| Discount Schedule | APC1 | |
| GTIN | 731304325116 | |
| Returnability | No | |

Packing Units

| Unit Type of Package 1 | PCE | |
|------------------------------|-----------------------|--|
| Number of Units in Package 1 | 1 | |
| Package 1 Height | 7.72 in (19.6 cm) | |
| Package 1 Width | 6.61 in (16.8 cm) | |
| Package 1 Length | 14.29 in (36.3 cm) | |
| Package 1 Weight | 8.40 lb(US) (3.81 kg) | |
| SCC14 | 10731304325113 | |

Contractual warranty

Warranty 3 years repair or replace



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint

Environmental Disclosure

Product Environmental Profile

Use Better

| EU RoHS Directive | Compliant with Exemptions |
|-----------------------------|---|
| REACh Regulation | REACh Declaration |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| ₩ Energy efficiency | |
| Optimized Energy Efficiency | Energy efficient product |

Use Again

| ○ Repack and remanufacture | |
|----------------------------|-------------------------|
| Circularity Profile | End of Life Information |
| Removable battery | User replaceable |
| Take-back | Yes |