

Product data sheet

Specifications



APC Replacement Battery Cartridge 114 with 2 Year Warranty

APCRBC114

Overview

Lead time Usually in Stock

Main

Product or Component Type Replacement battery cartridge

Battery Type Lead-Acid battery

Provided Equipment All required connectors
Battery recycling guide
Installation guide
Reusable packaging

Batteries & Runtime

Battery Placement Internal Battery

Battery Slots Empty 0

Included Battery Modules 0

Device mounting Enclosed battery cartridge

Battery Voltage 12 V

RBC Quantity 1

Physical

Color Black

Height 3.9 in (100 mm)

Width 2.09 in (53 mm)

Depth 6.02 in (153 mm)

Net Weight 3.20 lb(US) (1.45 kg)

Mounting Mode Not rack-mountable

USB compatible No

Output

Battery Capacity 6.4 Ah

Environmental

Ambient Air Temperature for Operation 32...104 °F (0...40 °C)

Operating altitude 0...10000 ft

Relative Humidity 0...95 %

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| | |
|-------------------------------------|----------------------------|
| Ambient Air Temperature for Storage | 23...113 °F (-5...45 °C) |
| Storage altitude | 0...50000 ft (0...15240 m) |
| Storage Relative Humidity | 0...95 % |

Ordering and shipping details

| | |
|------|--------------|
| GTIN | 731304264385 |
|------|--------------|

Packing Units

| | |
|------------------------|---------------------|
| Unit Type of Package 1 | PCE |
| Nbr. of units in pkg. | 1 |
| Package 1 Height | 7.008 in (17.8 cm) |
| Package 1 Width | 3.3 in (8.5 cm) |
| Package 1 Length | 8.3 in (21 cm) |
| Package weight(Lbs) | 3.7 lb(US) (1.7 kg) |
| SCC14 | 10731304264382 |

Contractual warranty

| | |
|----------------------|----|
| Warranty (in months) | 24 |
|----------------------|----|



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

| | |
|--|---|
| Total lifecycle Carbon footprint | 10 kg CO2 eq. |
| Carbon footprint of the manufacturing phase [A1 to A3] | 5 kg CO2 eq. |
| Carbon footprint of the distribution phase [A4] | 0.2 kg CO2 eq. |
| Carbon footprint of the installation phase [A5] | 0.1 kg CO2 eq. |
| Carbon footprint of the use phase [B2, B3, B4, B6] | 0.5 kg CO2 eq. |
| Carbon footprint of the end-of-life phase [C1 to C4] | 4 kg CO2 eq. |
| Environmental Disclosure | Product Environmental Profile |

Use Better



Materials and Substances

| | |
|--|--|
| Packaging made with recycled cardboard | Yes |
| Packaging without single use plastic | No |
| EU RoHS Directive | Compliant |
| REACH Regulation | Reference contains Substances of Very High Concern above the threshold |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |

Use Longer



Lifetime extension

| | |
|--------|----|
| Repair | No |
|--------|----|

Use Again



Repack and remanufacture

| | |
|-------------------------------|--|
| Recyclability potential, in % | 1 |
| Circularity Profile | End of Life Information |
| Take-back | Nej |
| WEEE Label |  The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |

Image of product / Alternate images

Alternative

