

Product data sheet

Specifications



APC NetShelter Basic Rack PDU, Vertical, 220-240V, 32A, 20 C13 and 6 C19 outlet

AP6009A

Overview

Lead time Usually in Stock

Main

Product or Component Type	PDU
PDU Type	Basic
Cord length	9.8 ft (3 m)
Number of cables	1
Provided Equipment	Installation guide Safety guide

Complementary

Input Voltage	230 V
Height	64.02 in (1626 mm)
Width	2.2 in (56 mm)
Output Voltage	230 V
Depth	1.7 in (43 mm)
Net Weight	13.62 lb(US) (6.18 kg)
Mounting Location	Side
Mounting preference	No preference
Input Plug Type	IEC 60309 32 A 2P+E
Mounting Mode	Not rack-mountable
Rack units	0U
Mounting position	Vertical
permissible voltage	200...240 V
Input current limits	32 A
Load Capacity	7400 VA
Input Frequency	50/60 Hz
Outlet type and quantity	20 IEC 60320 C13 6 IEC 60320 C19

Environment

Product Certifications	CE EAC IRAM VDE
------------------------	--------------------------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ambient Air Temperature for Operation	32...122 °F (0...50 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5...149 °F (-15...65 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 ft (0...15240 m)

Ordering and shipping details

GTIN	731304327783
-------------	--------------

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	73.8 in (187.5 cm)
Package 1 Width	5.3 in (13.5 cm)
Package 1 Length	8.9 in (22.6 cm)
Package weight(Lbs)	17.6 lb(US) (8 kg)

Contractual warranty

Warranty (in months)	24
-----------------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Total lifecycle Carbon footprint	4 481 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	0.6 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	0.6 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	4 452 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	0.5 kg CO2 eq.
Environmental Disclosure	Product Environmental Profile

Use Better



Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
SCIP Number	1cdb2fed-a06f-4574-913d-8df8e70936b2
EU RoHS Directive	Compliant
REACH Regulation	Free of Substances of Very High Concern above the threshold
Halogen content performance	Product contains halogen above thresholds

Use Longer



Lifetime extension

Repair	No
--------	----

Use Again



Repack and remanufacture

Recyclability potential, in %	45
Circularity Profile	End of Life Information
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Image of product / Alternate images

Alternative

