

Product data sheet

Specifications



APC NetShelter Basic Rack PDU, Half Height, 100-240V/20A, 220-240V/16A, 14 C13 outlet

AP6003A

Overview

Lead time Usually in Stock

Main

Color Black

Product or Component Type PDU

PDU Type Basic

Provided Equipment Installation guide
Safety guide

Complementary

Input Voltage 230 V

Height 20.6 in (523 mm)

Width 2.2 in (56 mm)

Output Voltage 100 V
120 V
200 V
208 V
230 V
240 V

Depth 1.9 in (47 mm)

Net Weight 4.14 lb(US) (1.88 kg)

Mounting Location Side

Mounting preference Lower

Input Plug Type IEC 60320 C20

Mounting Mode Not rack-mountable

Rack units 0U

USB compatible No

Mounting position Vertical

Line Rated Current 16 A

permissible voltage 100...240 V

Max line current 20 A

Input current limits 20 A

Load Capacity 3300 VA

Input Frequency 50/60 Hz

Outlet type and quantity 14 IEC 60320 C13

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Environment

| | |
|--|----------------------------|
| Product Certifications | cUL Listed UL Listed |
| Ambient Air Temperature for Operation | 32...122 °F (0...50 °C) |
| Relative Humidity | 5...95 % |
| Operating altitude | 0...10000 ft |
| Ambient Air Temperature for Storage | 5...149 °F (-15...65 °C) |
| Storage Relative Humidity | 5...95 % |
| Storage altitude | 0...50000 ft (0...15240 m) |

Ordering and shipping details

| | |
|-------------|--------------|
| GTIN | 731304327769 |
|-------------|--------------|

Packing Units

| | |
|-------------------------------|-----------------------|
| Unit Type of Package 1 | PCE |
| Nbr. of units in pkg. | 1 |
| Package 1 Height | 24.09 in (61.2 cm) |
| Package 1 Width | 4.2 in (10.7 cm) |
| Package 1 Length | 4.8 in (12.3 cm) |
| Package weight(Lbs) | 5.62 lb(US) (2.55 kg) |
| SCC14 | 10731304327766 |

Contractual warranty

| | |
|-----------------------------|----|
| Warranty (in months) | 24 |
|-----------------------------|----|



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

| | |
|--|---|
| Total lifecycle Carbon footprint | 1 748 kg CO2 eq. |
| Carbon footprint of the manufacturing phase [A1 to A3] | 0.2 kg CO2 eq. |
| Carbon footprint of the distribution phase [A4] | 0.2 kg CO2 eq. |
| Carbon footprint of the installation phase [A5] | 0 kg CO2 eq. |
| Carbon footprint of the use phase [B2, B3, B4, B6] | 1 739 kg CO2 eq. |
| Carbon footprint of the end-of-life phase [C1 to C4] | 0.2 kg CO2 eq. |
| Environmental Disclosure | Product Environmental Profile |

Use Better



Materials and Substances

| | |
|--|---|
| Packaging made with recycled cardboard | Yes |
| Packaging without single use plastic | No |
| SCIP Number | 1cdb2fed-a06f-4574-913d-8df8e70936b2 |
| EU RoHS Directive | Compliant |
| REACH Regulation | Free of Substances of Very High Concern above the threshold |
| Halogen content performance | Product contains halogen above thresholds |

Use Longer



Lifetime extension

| | |
|--------|----|
| Repair | No |
|--------|----|

Use Again



Repack and remanufacture

| | |
|-------------------------------|--|
| Recyclability potential, in % | 45 |
| Circularity Profile | End of Life Information |
| Take-back | No |
| WEEE Label |  The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |

Image of product / Alternate images

Alternative



