

# Product data sheet

Specifications



## Power Cord Kit (6 ea), Locking, C19 to C20, 1.2m, Blue

AP8714SX592

### Overview

Lead time Usually in Stock

### Main

Product or Component Type Power cord  
Input Connection Type IEC 60320 C20  
Cable length 3.97 ft (1.21 m)  
Number of cables 6

### Physical

Color Blue  
Height 11.8 in (300 mm)  
Width 2.8 in (70 mm)  
Depth 2.8 in (70 mm)  
Net Weight 3.62 lb(US) (1.64 kg)  
Mounting preference No preference  
Mounting Mode Not rack-mountable

### Input

Max line current 16 A  
Input current limits 16 A

### Output

Maximum Total Current Draw per Phase 16 A  
Number of power socket outlets 1 IEC 60320 C19  
Cord Length 4 ft (1.2 m)

### Conformance

Product Certifications CCC  
CSA  
PSE  
UL Listed  
VDE

### Environmental

Ambient Air Temperature for Operation 32...167 °F (0...75 °C)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Relative Humidity	20...80 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...167 °F (-25...75 °C)
Storage Relative Humidity	20...80 %
Storage altitude	0...50000 ft (0...15240 m)

## Ordering and shipping details

GTIN	731304285007
Country of origin	CN

## Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	11.8 in (30 cm)
Package 1 Width	2.8 in (7 cm)
Package 1 Length	2.8 in (7 cm)
Package weight(Lbs)	3.62 lb(US) (1.64 kg)
SCC14	10731304285004

## Contractual warranty

Warranty (in months)	24
----------------------	----



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



### Environmental footprint

Total lifecycle Carbon footprint	143 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	8 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	0.1 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0.7 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	132 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	3 kg CO2 eq.
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Use Better



### Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
SCIP Number	1cdb2fed-a06f-4574-913d-8df8e70936b2
EU RoHS Directive	<a href="#">Compliant</a>
REACH Regulation	<a href="#">Free of Substances of Very High Concern above the threshold</a>
Halogen content performance	Product contains halogen above thresholds

## Use Longer



### Lifetime extension

Repair	No
--------	----

## Use Again



### Repack and remanufacture


Recyclability potential, in %	30
Circularity Profile	<a href="#">End of Life Information</a>
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Image of product / Alternate images

Alternative

---

