

Product data sheet

Specifications



APC NetShelter Basic Rack PDU,
0U/1U, 120-240V/15A, 220-240V/
10A, 8 C13 outlet

AP6015A

Overview

Lead time	Usually in Stock
-----------	------------------

Main

Color	Black
Product or Component Type	PDU
PDU Type	Basic
Provided Equipment	Installation guide Safety guide

Complementary

Input Voltage	100 V 120 V 200 V 208 V 230 V 240 V
Height	9.4 in (240 mm)
Width	1.7 in (44 mm)
Output Voltage	100 V 120 V 200 V 208 V 230 V 240 V
Depth	3.7 in (93 mm)
Net Weight	2.006 lb(US) (0.91 kg)
Mounting Location	Front Rear
Mounting preference	No preference
Input Plug Type	IEC 60320 C14
Mounting Mode	Not rack-mountable
Rack units	1U
Mounting position	Horizontal
Line Rated Current	12 A
permissible voltage	100...240 V
Max line current	15 A
Input current limits	15 A
Load Capacity	2300 VA

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Input Frequency	50/60 Hz
Outlet type and quantity	8 IEC 60320 C13

Environment

Product Certifications	cUL Listed CE EAC IRAM UL Listed VDE
------------------------	---

Ordering and shipping details

GTIN	731304327790
------	--------------

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	11.3 in (28.6 cm)
Package 1 Width	5.1 in (13 cm)
Package 1 Length	8.3 in (21 cm)
Package weight(Lbs)	3.02 lb(US) (1.37 kg)
SCC14	10731304327797

Contractual warranty

Warranty (in months)	24
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Total lifecycle Carbon footprint	2 101 kg CO2 eq.
Environmental Disclosure	Product Environmental Profile
Carbon footprint of the manufacturing phase [A1 to A3]	0.1 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	0.1 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	2 096 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	0.1 kg CO2 eq.

Use Better



Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
SCIP Number	1cdb2fed-a06f-4574-913d-8df8e70936b2
EU RoHS Directive	Compliant
REACH Regulation	Free of Substances of Very High Concern above the threshold
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
Halogen content performance	Product contains halogen above thresholds

Use Longer



Lifetime extension

Repair	No
--------	----

Use Again



Repack and remanufacture

Recyclability potential, in %	45
Circularity Profile	End of Life Information
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Image of product / Alternate images

Alternative

