

APC Smart-UPS On-Line, 2200VA, Tower, 120V, 6x 5-20R+1x L5-20R NEMA outlets, SmartSlot, Extended runtime, W/O rail kit

SRT2200XLA

Product availability: Stock - Normally stocked in distribution facility

Overview

Presentation	High density, double-conversion on-line power protection with scalable runtime.
Lead time	Usually in Stock

Main

wan	
Main Input Voltage	120 V
Product or Component Type	Uninterruptible power supply (UPS)
Main Output Voltage	120 V
Kw Rating	1800 W
Rated power in VA	2200 VA
Input Connection Type	NEMA 5-20P
output connection type	6 NEMA 5-20R 1 NEMA L5-20R
Cable length	6 ft (1.8 m)
Number of cables	1
Provided equipment	Installation guide Removable support feet USB cable Warranty card
Range of Product	Smart-UPS On-Line

Batteries & Runtime

Run Time	View Runtime Graph ☐
Efficiency	View Efficiency Graph ☐
Battery Type	Lead-Acid battery
Battery Voltage	72V
Extendable Run Time	1
Included Battery Modules	1
Battery Slots Empty	0
Typical recharge time	3 h
RBC Quantity	1
Battery life	35 year(s)
Replacement battery	APCRBC141 ☐

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Battery Charge Power (Watts) 102 W rated

General

Number of power module	1400
Number of power module filled slots	0
Number of power module free slots	0
product web sub-family	High density
Redundant	No
Topology	Double Conversion Online

Physical

color	Black
Height	3.35 in (8.5 cm)
Width	17.01 in (43.2 cm)
Depth	22.99 in (58.4 cm)
Net Weight	55.1 lb(US) (25 kg)
Mounting Location	Front
Mounting preference	Lower
Mounting Mode	Not rack-mountable
Two post mountable	0
USB compatible	Yes
Mounting position	Vertical

Input

Input Frequency 40 - 70 Hz auto-sensing

Output

Bypass type	Internal Bypass (Automatic and Manual)
Crest factor	3:1
Harmonic distortion	Less than 2%
Maximum configurable power in VA	2200 VA
Max Configurable Power (Watts)	1800 W
Wave type	Sine wave
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains

Conformance

Product Certifications ENERGY STAR V2.0 (USA)

Environmental

Online Thermal Dissipation	535 Btu/h
Operating altitude	010000 ft
Ambient air temperature for operation	32104 °F (040 °C)

Ambient Air Temperature for Storage	5113 °F (-1545 °C)	
Storage altitude	050000 ft (0.000000000015240.0000000000 m)	
IP degree of protection	IP20	
Relative Humidity	095 % non-condensing	
Storage Relative Humidity	095 % non-condensing	

Communications & Management

Emergency Power Off (EPO)	Yes	
Free slots	1	
Alarm	Audible and visible alarms : prioritized by severity	

Surge Protection and Filtering

Surge energy rating 340 J

Ordering and shipping details

GTIN	731304325161
Returnability	No
Country of origin	PH

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.69 in (24.6 cm)
Package 1 Width	31.89 in (81 cm)
Package 1 Length	23.58 in (59.9 cm)
Package 1 Weight	67.99 lb(US) (30.84 kg)

Contractual warranty

Warranty 3 years repair or replace (excluding battery) and 2 years for battery



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	3353
Environmental Disclosure	Product Environmental Profile

Use Better

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
᠃ Energy efficiency	
Optimized Energy Efficiency	Energy efficient product
ENERGY STAR®	ENERGY STAR UPS V2.0 (USA)

Use Again

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Removable battery	User replaceable
Take-back	Yes