

Rack PDU, Basic, Zero U, 20A, 120V, (24)5-20

AP7530

Product availability: Stock - Normally stocked in distribution facility

Overview

Lead time Usually in Stock

Main

Color	Black	
Product or Component Type	PDU	
PDU Type	Basic	
Cord length	10 ft (3.05 m)	
Number of cables	1	
Provided Equipment	Cord retention bracket(s) Installation guide Rack Mounting brackets Toolless Mounting Kit User Manual	

Complementary

Input Voltage	100 V	
	120 V	
Height	63.74 in (161.9 cm)	
Width	2.20 in (5.6 cm)	
Output Voltage	120 V	
Depth	1.73 in (4.4 cm)	
Net Weight	10.71 lb(US) (4.86 kg)	
Mounting Location	Side	
Mounting preference	No preference	
Input Plug Type	NEMA L5-20P	
Mounting Mode	Rack-mounted	
Rack units	ou	
Mounting position	Vertical	
Line Rated Current	16 A	
Permissible voltage	100120 V	
Input current limits	20 A	
Load Capacity	1920 VA	
Input Frequency	50/60 Hz	
Outlet type and quantity	24 NEMA 5-20R	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Environment

Product Certifications	cUL Listed UL Listed	
Standards	CSA C22.2 No. 60950-1-03 UL 60950-1	
Ambient air temperature for operation	23113 °F (-545 °C)	
Relative Humidity	595 %	
Operating altitude	015000 ft	
Ambient Air Temperature for Storage	-13149 °F (-2565 °C)	
Storage Relative Humidity	595 %	
Storage altitude	050000 ft (0.000000000015240.0000000000 m)	

Ordering and shipping details

Category	11309-APC RESALE PRODUCTS	
Discount Schedule	APC1	
GTIN	731304207962	
Returnability	No	
Country of origin	IN	

Packing Units

Unit Type of Package 1	PCE	
Number of Units in Package 1	1	
Package 1 Height	84.02 in (213.4 cm)	
Package 1 Width	5.00 in (12.7 cm)	
Package 1 Length	5.98 in (15.2 cm)	
Package 1 Weight	12.72 lb(US) (5.77 kg)	
SCC14	731304207962	

Contractual warranty

Warranty 2 years repair or replace



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	120
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
EU RoHS Directive	Compliant
REACh Regulation	REACh Declaration
[⋄] Energy efficiency	
Optimized Energy Efficiency	Energy efficient product

Use Again

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Halogen content performance	Product contains halogen above thresholds
Take-back	Yes