

Product data sheet

Specifications

Rack PDU, Basic, 1U, 20A, 120V, (10)5-20, 5-20P



AP9563

Overview

Lead time	Usually in Stock
-----------	------------------

Main

Color	Black
Product or Component Type	PDU
PDU Type	Basic
Cord length	12 ft (3.7 m)
Number of cables	1
Provided Equipment	Installation guide Rack Mounting brackets

Complementary

Input Voltage	100 V 120 V
Height	1.73 in (4.4 cm)
Width	17.60 in (44.7 cm)
Output Voltage	120 V
Depth	2.24 in (5.7 cm)
Net Weight	5.5 lb(US) (2.5 kg)
Mounting Location	Front Rear
Mounting preference	No preference
Input Plug Type	NEMA 5-20P
Mounting Mode	Rack-mounted
Rack units	1U
Mounting position	Horizontal
Line Rated Current	16 A
Input current limits	20 A
Load Capacity	1920 VA
Input Frequency	50/60 Hz
Outlet type and quantity	10 NEMA 5-20R

Environment

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Product Certifications	cUL Listed UL Listed
Ambient air temperature for operation	23...113 °F (-5...45 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.0000000000...15240.0000000000 m)

Ordering and shipping details

GTIN	731304203889
------	--------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.76 in (7 cm)
Package 1 Width	9.02 in (22.9 cm)
Package 1 Length	18.27 in (46.4 cm)
Package 1 Weight	8.02 lb(US) (3.64 kg)

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	64
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
EU RoHS Directive	Compliant
REACH Regulation	REACH Declaration

Energy efficiency	
Optimized Energy Efficiency	Energy efficient product

Use Again

Repack and remanufacture	
Circularity Profile	End of Life Information
Halogen content performance	Product contains halogen above thresholds
Take-back	Yes