

APC Service Bypass Panel-200/208/240V; 100A; MBB; Hardwire input; (6) L14-30R output

SBP16KRMP4U

Overview

Lead time Usually in Stock

Main

Main Input Voltage	208 V
Product or Component Type	Bypass kit
Main Output Voltage	200 V 208 V
Other Output Voltage	240 V
Number of rack unit	4U
Provided Equipment	Installation guide Rack Mounting brackets User Manual
Range of Product	Maintenance Bypass Panels

Physical

Color	Black	
Height	7.01 in (17.8 cm)	
Width	17.01 in (43.2 cm)	
Depth	26.50 in (67.3 cm)	
Net Weight	51.10 lb(US) (23.18 kg)	
Mounting Location	Front	
Mounting preference	Lower	
Mounting Mode	Rack-mounted	

Input

Input Frequency	50/60 Hz	
Number of input connectors	1 Hard Wire 3-wire (2PH + G) 1 Hard Wire 4-wire (2PH+N+G)	
Max line current	100 A	
Input current limits	100 A	
Load Capacity	20000 VA	
Power factor	01	

Output

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Max current draw	100 A	
Number of power socket outlets	6 NEMA L14-30R	
Protection Type	Circuit breaker	
Efficiency	99 %	

Conformance

Product Certifications CSA GOST

Environmental

Ambient air temperature for operation	-4122 °F (-2050 °C)	
Relative Humidity	095 %	
Operating altitude	015000 ft	
Ambient Air Temperature for Storage	-40149 °F (-4065 °C)	
Storage Relative Humidity	095 %	
Storage altitude	050000 ft (0.000000000015240.000000000 m)	

Ordering and shipping details

GTIN 731304212669

Packing Units

Unit Type of Package 1	PCE	
Number of Units in Package 1	1	
Package 1 Height	12.01 in (30.5 cm)	
Package 1 Width	39.02 in (99.1 cm)	
Package 1 Length	24.02 in (61 cm)	
Package 1 Weight	74.16 lb(US) (33.64 kg)	

Contractual warranty

Warranty 2 years (parts only)



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Use Better

Take-back

EU RoHS Directive	Compliant
REACh Regulation	REACh Declaration
China RoHS Regulation	China RoHS declaration
Use Again	
○ Repack and remanufacture	

No