Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Rack PDU, Basic, ZeroU, 5.7kW, 120V, (42) 5-20; 10 Cord

AP7592

Overview

Lead time	Usually in Stock

Main

Color	Black
Product or Component Type	PDU
PDU Type	Basic
Cord length	10 ft (3.05 m)
Number of cables	1
Provided Equipment	Installation guide Rack Mounting brackets Toolless Mounting Kit

Complementary

Input Voltage	208 V 3 phase
Height	70.00 in (177.8 cm)
Width	2.20 in (5.6 cm)
Output Voltage	120 V
Depth	1.73 in (4.4 cm)
Net Weight	12.28 lb(US) (5.57 kg)
Mounting Location	Side
Mounting preference	No preference
Input Plug Type	NEMA L21-20P
Mounting Mode	Rack-mounted
Rack units	0U
Mounting position	Vertical
Line Rated Current	16 A
Input current limits	20 A
Load Capacity	5700 VA
Input Frequency	50/60 Hz
Outlet type and quantity	42 NEMA 5-20R

Environment

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Product Certifications	cUL Listed UL Listed	
Standards	CSA C22.2 No. 60950-1-03 UL 60950-1	
Ambient air temperature for operation	32113 °F (045 °C)	
Relative Humidity	595 %	
Operating altitude	010000 ft	
Ambient Air Temperature for Storage	-13149 °F (-2565 °C)	
Storage Relative Humidity	595 %	
Storage altitude	050000 ft (0.000000000015240.0000000000 m)	

Ordering and shipping details

GTIN 731304223085

Packing Units

_	
Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	84.02 in (213.4 cm)
Package 1 Width	5.00 in (12.7 cm)
Package 1 Length	5.98 in (15.2 cm)
Package 1 Weight	19.53 lb(US) (8.86 kg)

Contractual warranty

Warranty 2 years repair or replace



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability

Provious Environmental footprint

Environmental Disclosure

Product Environmental Profile

Use Better

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant
REACh Regulation	REACh Declaration
[⋄] Energy efficiency	
Optimized Energy Efficiency	Energy efficient product

Use Again

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Halogen content performance	Product contains halogen above thresholds
Take-back	Yes