

Product data sheet

Specifications



APC NetShelter Switched Rack PDU, 1U, 1PH, 2.3kW 230V 10A or 2.5kW 208V 12A, 8 C13 outlets, C14 cord

AP7920B

Overview

Presentation This APC Switched Rack PDU power distribution unit has a wide range of standardized PDU features that increase network efficiency, manageability and functionality. The output and input connections are (8)C13. Network management capabilities allow you to configure and manage rack PDUs from remote locations. It has a local current monitoring display that gives a visible warning in case of an overload. The remote individual outlet control provides real-time monitoring of connected loads. It has a multi-tier user access that enables you to restrict unauthorized use of outlets. This rack has a single input power source making it easy to install.

Lead time Usually in Stock

Main

Color	Black
Product or Component Type	PDU
PDU Type	Switched
Cord length	6.2 ft (1.9 m)
Number of cables	1
Provided Equipment	Installation guide Rack Mounting brackets User Manual

Complementary

Input Voltage	200 V 208 V 230 V
Height	1.7 in (44 mm)
Width	17.5 in (445 mm)
Output Voltage	208 V 230 V
Depth	4.3 in (108 mm)
Net Weight	5.004 lb(US) (2.27 kg)
Mounting Location	Front Rear
Mounting preference	No preference
Input Plug Type	IEC 60320 C14
Mounting Mode	Rack-mounted
Rack units	1U
Mounting position	Horizontal
Line Rated Current	12 A

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

permissible voltage	200...240 V
Input current limits	15 A
Load Capacity	2300 VA
Different voltages and corresponding amperages	10 A - 230 V 12 A - 208 V
Input Frequency	50/60 Hz
Outlet type and quantity	8 IEC 60320 C13

Environment

Product Certifications	cUL Listed CE CSA GOST IRAM UL Listed VDE
Standards	EN 55022 Class A EN 55024 EN 61000-3-2 EN 61000-3-3 UL 60950
Ambient Air Temperature for Operation	32...113 °F (0...45 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0...15240 m)

Ordering and shipping details

GTIN	731304331612
Country of origin	IN

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	2.756 in (7.000 cm)
Package 1 Width	19.291 in (49.000 cm)
Package 1 Length	13.583 in (34.500 cm)
Package weight(Lbs)	8.247 lb(US) (3.741 kg)
Unit Type of Package 2	P06
Number of Units in Package 2	17
Package 2 Height	29.921 in (76.000 cm)
Package 2 Width	23.622 in (60.000 cm)
Package 2 Length	31.496 in (80.000 cm)
Package 2 Weight	143.301 lb(US) (65.000 kg)

Contractual warranty



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Total lifecycle Carbon footprint	1 221 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	19 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	0.1 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0.5 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	1 200 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	1 kg CO2 eq.
Environmental Disclosure	Product Environmental Profile

Use Better



Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
SCIP Number	1cdb2fed-a06f-4574-913d-8df8e70936b2
EU RoHS Directive	Compliant By Exemption
REACH Regulation	Free of Substances of Very High Concern above the threshold
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov

Use Longer



Lifetime extension

Repair	No
--------	----

Use Again



Repack and remanufacture

Recyclability potential, in %	71
Circularity Profile	End of Life Information
Removable battery	Yes
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Image of product / Alternate images

Alternative



