

APC Service Bypass Panel-100-120V; 30A; BBM; L5-30P input; (2) 5-20R (6) 5-15R output

SBP3000RM2U

Product availability: Stock - Normally stocked in distribution facility

Overview

Lead time Usually in Stock

Main

IVIAIII	
Main Input Voltage	100 V
	120 V
Product or Component Type	Bypass kit
Main Output Voltage	100 V
	120 V
Other Output Voltage	110 V
Input Connection Type	NEMA L5-30P
Number of rack unit	2U
Cable length	10 ft (3.05 m)
Number of cables	1
Provided Equipment	Installation guide
	Rack Mounting brackets
	User Manual
Range of Product	Maintenance Bypass Panels

Physical

Color	Black
Height	3.50 in (8.9 cm)
Width	17.01 in (43.2 cm)
Depth	25.51 in (64.8 cm)
Net Weight	30.07 lb(US) (13.64 kg)
Mounting Location	Front
Mounting preference	Lower
Mounting Mode	Rack-mounted

Input

Input Frequency	50/60 Hz
Max line current	24 A
Input current limits	24 A
Load Capacity	3000 VA
Power factor	01

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Output

Max current draw	30 A
Number of power socket outlets	6 NEMA 5-15R 2 NEMA 5-20R
Protection Type	Circuit breaker
Cord Length	10 ft (3.05 m)
Efficiency	99 %

Conformance

Product Certifications	CSA	
	GOST	

Environmental

Ambient air temperature for operation	-4122 °F (-2050 °C)	
Relative Humidity	095 %	
Operating altitude	015000 ft	
Ambient Air Temperature for Storage	-13149 °F (-2565 °C)	
Storage Relative Humidity	095 %	
Storage altitude	050000 ft (0.000000000015240.0000000000 m)	

Ordering and shipping details

Category	80230-IG SEBA TO SEUSA	
Discount Schedule	BMS1	
GTIN	731304212577	
Returnability	No	
Country of origin	PH	

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.99 in (20.3 cm)
Package 1 Width	39.02 in (99.1 cm)
Package 1 Length	24.02 in (61 cm)
Package 1 Weight	54.15 lb(US) (24.56 kg)

Contractual warranty

Warranty	2 years (parts only)



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Use Better

EU RoHS Directive	Compliant with Exemptions	
China RoHS Regulation	China RoHS declaration	
Use Again		
○ Repack and remanufacture		