

# Product data sheet

Specifications



## APC NetShelter Power Cord, C19 to IEC309 16A, 2.5m



AP9876

**Product availability: Non-Stock - Not normally stocked in distribution facility**

### Overview

Lead time Usually in Stock

### Main

Product or Component Type Power cord  
Input Connection Type IEC 60309 16 A  
Cable length 7.9 ft (2.4 m)  
Number of cables 1

### Physical

Color Black  
Net Weight 0.53 lb(US) (0.24 kg)  
Mounting preference No preference  
Mounting Mode Not rack-mountable

### Input

Input Frequency 50/60 Hz  
permissible voltage 90...250 V  
Max line current 16 A  
Input current limits 16 A

### Output

Maximum Total Current Draw per Phase 16 A  
Number of power socket outlets 1 IEC 60320 C19  
Protection Type Without circuit breaker

### Conformance

Product Certifications VDE

### Environmental

Ambient Air Temperature for Operation 32...113 °F (0...45 °C)  
Relative Humidity 0...95 %  
Operating altitude 0...10000 ft  
Ambient Air Temperature for Storage -13...149 °F (-25...65 °C)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0...15240 m)

## Ordering and shipping details

Category	11309-APC RESALE PRODUCTS
Discount Schedule	APC1
GTIN	731304189398
Returnability	No
Country of origin	CN

## Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	2.008 in (5.1 cm)
Package 1 Width	4.02 in (10.2 cm)
Package 1 Length	8.0 in (20.3 cm)
Package weight(Lbs)	0.659 lb(US) (0.299 kg)
Unit Type of Package 2	CAR
Number of Units in Package 2	10
Package 2 Height	9.2 in (23.3 cm)
Package 2 Width	12.8 in (32.5 cm)
Package 2 Length	20.9 in (53 cm)
Package 2 Weight	11.2 lb(US) (5.1 kg)
Unit Type of Package 3	PAL
Number of Units in Package 3	10
Package 3 Height	56.69 in (143.99 cm)
Package 3 Width	39.4 in (100 cm)
Package 3 Length	47.2 in (120 cm)
Package 3 Weight	11.2 lb(US) (5.1 kg)

## Contractual warranty

Warranty (in months)	24
----------------------	----



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



### Environmental footprint

Total lifecycle Carbon footprint	32 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	1 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	0 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0.1 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	30 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	0.4 kg CO2 eq.
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

### Use Better



### Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
SCIP Number	1cdb2fed-a06f-4574-913d-8df8e70936b2
EU RoHS Directive	<a href="#">Compliant</a>
REACH Regulation	<a href="#">Free of Substances of Very High Concern above the threshold</a>
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
Halogen content performance	Product contains halogen above thresholds

### Use Longer



### Lifetime extension

Repair	No
--------	----

### Use Again



### Repack and remanufacture

Recyclability potential, in %	30
Circularity Profile	<a href="#">End of Life Information</a>
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Image of product / Alternate images

Alternative

---

