

Product data sheet

Specifications



APC NetShelter Power Cord, IEC C19 to C20, 2.0m



AP9877

Product availability: Non-Stock - Not normally stocked in distribution facility

Overview

Lead time Usually in Stock

Main

Product or Component Type Power cord
Input Connection Type IEC 60320 C20
Cable length 6.50 ft (1.98 m)
Number of cables 1

Physical

Color Black
Net Weight 0.79 lb(US) (0.36 kg)
Mounting preference No preference
Mounting Mode Not rack-mountable

Input

Max line current 20 A
Input current limits 20 A

Output

Maximum Total Current Draw per Phase 20 A
Number of power socket outlets 1 IEC 60320 C19

Ordering and shipping details

Category 11309-APC RESALE PRODUCTS
Discount Schedule APC1
GTIN 731304198765
Returnability No
Country of origin US

Packing Units

Unit Type of Package 1 PCE
Nbr. of units in pkg. 1
Package 1 Height 12.008 in (30.5 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Width	4.02 in (10.2 cm)
Package 1 Length	4.02 in (10.2 cm)
Package weight(Lbs)	1.012 lb(US) (0.459 kg)
Unit Type of Package 2	CAR
Number of Units in Package 2	5
Package 2 Height	9.3 in (23.6 cm)
Package 2 Width	13.0 in (32.9 cm)
Package 2 Length	20.9 in (53.1 cm)
Package 2 Weight	6.99 lb(US) (3.17 kg)
Unit Type of Package 3	PAL
Number of Units in Package 3	5
Package 3 Height	56.69 in (143.99 cm)
Package 3 Width	39.4 in (100 cm)
Package 3 Length	47.2 in (120 cm)
Package 3 Weight	6.99 lb(US) (3.17 kg)

Contractual warranty

Warranty (in months)	24
-----------------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Total lifecycle Carbon footprint	39 kg CO2 eq.
Environmental Disclosure	Product Environmental Profile
Carbon footprint of the manufacturing phase [A1 to A3]	2 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	0 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0.2 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	36 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	0.6 kg CO2 eq.

Use Better



Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
SCIP Number	1cdb2fed-a06f-4574-913d-8df8e70936b2
EU RoHS Directive	Compliant
REACH Regulation	Free of Substances of Very High Concern above the threshold
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
Halogen content performance	Product contains halogen above thresholds

Use Longer



Lifetime extension

Repair	No
--------	----

Use Again



Repack and remanufacture

Recyclability potential, in %	30
Circularity Profile	End of Life Information
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Image of product / Alternate images

Alternative

