

APC Smart-UPS, Line Interactive, 1000VA, Tower, 120V, 8x NEMA 5-15R outlets, SmartConnect Port+SmartSlot, AVR, LCD

SMT1000C

Overview

Presentation	Intelligent and efficient network power protection from entry level to scalable runtime. Ideal UPS for servers, point-of-sale, routers, switches, hubs and other network devices.
Lead time	Usually in Stock
Main	
Main Input Voltage	120 V
Other Input Voltage	110 V 125 V
Main Output Voltage	120 V
Other Output Voltage	110 V 125 V
Kw Rating	700 W
Rated power in VA	1000 VA
Product or Component Type	Uninterruptible power supply (UPS)
Input Connection Type	NEMA 5-15P
output connection type	8 NEMA 5-15R
Cable length	6 ft (1.8 m)
Number of cables	1
Battery Type	Lead-Acid battery
Provided equipment	User Manual USB cable
Range of Product	Smart-UPS

Complementary

Communication port type	SmartConnect Ethernet port SmartSlot
Software package	SmartConnect software for remote power monitoring feature availability varies by terms of use

Batteries & Runtime

Run Time	View Runtime Graph ☐
Efficiency	View Efficiency Graph ☐
Extendable Run Time	0
Included Battery Modules	0

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Battery Slots Empty	0
Typical recharge time	3 h
RBC Quantity	1
Battery life	35 year(s)
Replacement battery	RBC6 □
Battery Charge Power (Watts)	88 W rated

General

Number of power module	0
Number of power module filled slots	0
Number of power module free slots	0
product web sub-family	Cloud-enabled monitoring
Redundant	No

Physical

color	Black
Height	8.62 in (21.9 cm)
Width	6.73 in (17.1 cm)
Depth	17.28 in (43.9 cm)
Net Weight	44.3 lb(US) (20.1 kg)
Mounting Location	Front
Mounting preference	No preference
Mounting Mode	Not rack-mountable
Two post mountable	0
USB compatible	Yes

Input

Efficiency at full load	75154 V adjustable 82144 V
Input Frequency	50/60 Hz +/- 3 Hz auto-sensing

Output

Harmonic distortion	Less than 5%
Maximum configurable power in VA	1000 VA
Max Configurable Power (Watts)	700 W
Transfer Time	6ms typical : 10ms maximum
Topology	Line Interactive
Wave type	Sine wave
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains

Conformance

Product Certifications	cULus
	ENERGY STAR V2.0 (USA)

Equipment protection policy Lifetime: \$150000

Environmental

Acoustic level	41 dBA
Online Thermal Dissipation	175 Btu/h
Operating altitude	010000 ft
Ambient air temperature for operation	32104 °F (040 °C)
Ambient Air Temperature for Storage	5113 °F (-1545 °C)
Storage altitude	050000 ft (0.000000000015240.0000000000 m)
Relative Humidity	095 %
Storage Relative Humidity	095 %

Communications & Management

control panel	Multi-function LCD status and control console
Free slots	1
Communication port support	SmartConnect Ethernet port: for cloud monitoring feature availability varies by terms of use
Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays

Surge Protection and Filtering

Surge energy rating	680 J
Filtering	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : m

Ordering and shipping details

Category	11309 - APC RESALE PRODUCTS	
GTIN	731304322771	
Returnability	No	
Country of origin	PH	

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	12.99 in (33 cm)
Package 1 Width	23.23 in (59 cm)
Package 1 Length	12.99 in (33 cm)
Package 1 Weight	49.91 lb(US) (22.64 kg)

Contractual warranty

Warranty 3 years repair or replace (excluding battery) and 2 years for battery



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	995
Environmental Disclosure	Product Environmental Profile

Use Better

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
SCIP Number	B2b22a56-41f2-497e-9ea6-cf093b3b8bd3
California proposition 65	"WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov"
♥ Energy efficiency	
Optimized Energy Efficiency	Energy efficient product
ENERGY STAR®	ENERGY STAR UPS V2.0 (USA)

Use Again

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Removable battery	User replaceable
Take-back	Yes