

Product data sheet

Specifications



Rack PDU, Basic, Zero U, 12.5kW, 208V, (30)C13, (6)C19; 3 Cord

AP7568

Overview

Lead time	Usually in Stock
-----------	------------------

Main

Color	Black
Product or Component Type	PDU
PDU Type	Basic
Cord length	3 ft (0.9 m)
Number of cables	1
Provided Equipment	Cord retention bracket(s) Documentation CD Installation guide Rack Mounting brackets Toolless Mounting Kit

Complementary

Input Voltage	208 V 3 phase
Height	70.00 in (177.8 cm)
Width	2.20 in (5.6 cm)
Output Voltage	208 V
Depth	3.50 in (8.9 cm)
Net Weight	15.32 lb(US) (6.95 kg)
Mounting Location	Side
Mounting preference	No preference
Mounting Mode	Rack-mounted
Rack units	0U
Mounting position	Vertical
Max line current	35 A
Input current limits	35 A
Load Capacity	12500 VA
Input Frequency	50/60 Hz
Number of input connectors	1 CS8365
Outlet type and quantity	30 IEC 60320 C13 6 IEC 60320 C19

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Product Certifications	cUL Listed UL Listed
Standards	CSA C22.2 No. 60950-1-03 UL 60950-1
Ambient air temperature for operation	23...113 °F (-5...45 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 ft (0.0000000000...15240.0000000000 m)

Ordering and shipping details

GTIN	731304226833
------	--------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	82.99 in (210.8 cm)
Package 1 Width	5.00 in (12.7 cm)
Package 1 Length	5.98 in (15.2 cm)
Package 1 Weight	22.42 lb(US) (10.17 kg)

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	179
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
EU RoHS Directive	Compliant
REACH Regulation	REACH Declaration

Energy efficiency	
Optimized Energy Efficiency	Energy efficient product

Use Again

Repack and remanufacture	
Circularity Profile	End of Life Information
Halogen content performance	Product contains halogen above thresholds
Take-back	Yes