

Product data sheet

Specifications



APC Smart-UPS C, Line Interactive, 1440VA, Tower, 120V, 8x NEMA 5-15R outlets, SmartConnect port, USB and Serial communication, AVR, Graphic LCD

SMC1500C

Product availability: Non-Stock - Not normally stocked in distribution facility

Overview

Lead time Usually Ships within 2 Weeks

Main

| | |
|----------------------------------|-------------------------------------|
| Main Input Voltage | 120 V AC |
| Other Input Voltages | 110 V 125 V |
| Input Connection Type | NEMA 5-15P |
| Efficiency at full load | 85...136 V adjustable 93...130 V |
| Input Frequency | 50/60 Hz +/- 3 Hz auto-sensing |
| Output voltage | 120 V AC 1 phase |
| Other Output Voltages | 110 V 125 V |
| Rated power in W | 900 W |
| rated power in VA | 1440 VA |
| output connection type | 8 NEMA 5-15R |
| Harmonic distortion | Less than 5% |
| Maximum configurable power in VA | 1440 VA |
| Max Configurable Power (Watts) | 900 W |
| Transfer Time | 6ms typical : 10ms maximum |
| Topology | Line Interactive |
| Waveform Type | Sine wave |
| Output Frequency (sync to mains) | 50/60 Hz +/- 3 Hz sync to mains |

Complementary

| | |
|---------------|---|
| Battery Size | Lead-acid internal included |
| Control panel | Multi-function LCD status and control console |
| Free slots | 0 |
| Alarm | Alarm when on battery : distinctive low battery alarm : configurable delays |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| | |
|--|--|
| UPS connectivity | Serial port USB port SmartConnect port |
| Communication port support | SmartConnect Ethernet port: for cloud monitoring feature availability varies by terms of use |
| Software package | SmartConnect software for remote power monitoring feature availability varies by terms of use |
| Surge energy rating | 680 J |
| Filtering | Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : m |
| Cable length | 6 ft (1.8 m) |
| Number of cables | 1 |
| color | Black |
| Height | 8.6 in (219 mm) |
| Width | 6.7 in (171 mm) |
| Depth | 17.3 in (439 mm) |
| Net Weight | 44.3 lb(US) (20.1 kg) |
| Mounting Location | Front |
| Mounting preference | No preference |
| Mounting Mode | Not rack-mountable |
| Two post mountable | 0 |
| USB compatible | Yes |
| Mounting mode | Tower |
| Provided equipment | USB cable |
| Number of power module | 0 |
| Number of power module filled slots | 0 |
| Number of power module free slots | 0 |
| Additional specification | Cloud-enabled monitoring |
| Redundant | No |
| Range of Product | Smart-UPS |
| Product or Component Type | Uninterruptible power supply (UPS) |

Environment

| | |
|--|---------------------------------|
| Product Certifications | cULus ENERGY STAR V2.0 (USA) |
| Equipment protection policy | Lifetime : \$150000 |
| Ambient Air Temperature for Operation | 32...104 °F (0...40 °C) |
| Ambient Air Temperature for Storage | 5...113 °F (-15...45 °C) |
| Storage altitude | 0...50000 ft (0...15240 m) |
| Relative Humidity | 0...95 % |
| Storage Relative Humidity | 0...95 % |
| Acoustic level | 45 dBA |
| Heat dissipation | 225 Btu/h |

| | |
|--------------------|--------------|
| Operating altitude | 0...10000 ft |
|--------------------|--------------|

Batteries & Runtime

| | |
|------------------------------|---|
| Run Time | View Runtime Graph  |
| Efficiency | View Efficiency Graph  |
| Battery Type | Lead-Acid battery |
| Extendable Run Time | 0 |
| Included Battery Modules | 0 |
| Battery Slots Empty | 0 |
| Typical recharge time | 3 h |
| RBC Quantity | 1 |
| Battery Life | 3...5 year(s) |
| Replacement battery | RBC6  |
| Battery Charge Power (Watts) | 96 W rated |

Ordering and shipping details

| | |
|-------------------|-----------------------------|
| Category | 11309 - APC RESALE PRODUCTS |
| GTIN | 00731304322764 |
| Returnability | No |
| Country of origin | VN |

Packing Units

| | |
|------------------------|-------------------------|
| Unit Type of Package 1 | PCE |
| Nbr. of units in pkg. | 1 |
| Package 1 Height | 13.0 in (33 cm) |
| Package 1 Width | 23.2 in (59 cm) |
| Package 1 Length | 13.0 in (33 cm) |
| Package weight(Lbs) | 49.91 lb(US) (22.64 kg) |

Contractual warranty

| | |
|----------------------|----|
| Warranty (in months) | 24 |
|----------------------|----|



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

| | |
|--|---|
| Total lifecycle Carbon footprint | 831 kg CO2 eq. |
| Carbon footprint of the manufacturing phase [A1 to A3] | 614 kg CO2 eq. |
| Carbon footprint of the distribution phase [A4] | 15 kg CO2 eq. |
| Carbon footprint of the installation phase [A5] | 4 kg CO2 eq. |
| Carbon footprint of the use phase [B2, B3, B4, B6] | 175 kg CO2 eq. |
| Carbon footprint of the end-of-life phase [C1 to C4] | 22 kg CO2 eq. |
| Environmental Disclosure | Product Environmental Profile |

Use Better



Materials and Substances

| | |
|--|--|
| Packaging made with recycled cardboard | Yes |
| Packaging without single use plastic | No |
| SCIP Number | B2b22a56-41f2-497e-9ea6-cf093b3b8bd3 |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |



Energy efficiency

| | |
|-----------------------------|----------------------------|
| Optimized Energy Efficiency | Energy efficient product |
| ENERGY STAR® | ENERGY STAR UPS V2.0 (USA) |

Use Longer



Lifetime extension

| | |
|--------|----|
| Repair | No |
|--------|----|

Use Again



Repack and remanufacture

| | |
|-------------------------------|---|
| Recyclability potential, in % | 51 |
| Circularity Profile | End of Life Information |
| Removable battery | User replaceable |
| Take-back | Yes |

WEEE Label



The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Technical Illustration

Dimensions



Offer Marketing Illustration

Product benefits / Features



Secure, remote monitoring
So you can always be up to date on the status of your power infrastructure

Proactive lifecycle alerts
Maximize the lifespan of the UPS by firmware upgrades, recommendations on maintenance and warranty updates.

Cloud enabled as a standard
With built-in Ethernet port to make it easy and cost effective to monitor your UPS online

Offer Marketing Illustration

Product benefits / Features

Complete power protection for your business needs and electronics




APC Smart-UPS models protect entry level servers, networks, retail POS, and business VOIP from power disruptions, providing continuous power to maintain business productivity and continuity

Offer Marketing Illustration

Product benefits / Features

The first cloud enabled UPS for distributed IT

Monitor and manage your Smart-UPS with a cloud based software, EcoStruxure™ IT SmartConnect. 6 month free trial of the SmartConnect Standard plan included.

The image shows a desktop monitor, a laptop, a tablet, and a smartphone, all displaying the EcoStruxure IT SmartConnect web interface. The interface features a navigation menu on the left, a main content area with various status indicators and data points, and a clean, professional design. The devices are arranged on a light-colored surface with a subtle grid pattern.

Offer Marketing Illustration

Product benefits / Features



Life Is On | Schneider Electric

APC

APC Samrt-UPS

Connected backup power and protection for valuable IT equipment.

- 

EcoStruxure™ IT SmartConnect compatible
- 

Intelligent battery management
- 

High efficiency Green Mode
- 

Sine wave power

Image of product / Alternate images

Alternative

