

Product data sheet

Specifications



17" Rack LCD Console with Integrated 16 Port Analog KVM Switch

AP5816

Overview

Presentation The Rack LCD Console with Integrated KVM Switch combines the functionality of Rack LCD Console and Analog KVM switches in one convenient package optimizing U space in the rack environment, eliminating cable clutter, and offering a value of two products functionality in one package. Keyboard is a US English keyboard layout.

Lead time Usually in Stock

Main

Main Input Voltage	120 V 240 V
Input Connection Type	IEC 60320 C14
Number of rack unit	1U
Cable length	5.97 ft (1.82 m)
Number of cables	1
Provided equipment	USB KVM cable Single user rack mount kit PS2 KVM cable NEMA 5-15 power cord Installation guide Firmware upgrade cable Documentation CD C13-C14 power cord

Physical

Color	Black
Height	1.7 in (43 mm)
Width	19.02 in (483 mm)
Depth	24.2 in (614 mm)
Net Weight	30.9 lb(US) (14 kg)
Mounting Location	Front
Mounting preference	No preference
Mounting Mode	Rack-mounted
Maximum Mounting Depth	41.3 in (1049.8 mm)
Minimum Mounting Depth	26.8 in (680 mm)

Input

Input Frequency 50/60 Hz

Conformance

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Product Certifications	cUL Listed C-tick CE Industry Canada KCC UL Listed VDE TAA compliance
-------------------------------	--------------------------------------------------------------------------------------------

Standards	EN 60950 FCC Part 15 class A IEC 60950
------------------	----------------------------------------------

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
----------------------------------------------	-------------------------

Supported Hardware

Display colour	16 colours
-----------------------	------------

Display size	337.9 (H) x 270.3 (V) 17 inch
---------------------	----------------------------------

Trackball Type	PS/2 Touchpad USB mouse
-----------------------	----------------------------

Display Type	LCD display
---------------------	-------------

Ordering and shipping details

GTIN	731304278818
-------------	--------------

Packing Units

Unit Type of Package 1	PCE
-------------------------------	-----

Nbr. of units in pkg.	1
------------------------------	---

Package 1 Height	5.1 in (13 cm)
-------------------------	----------------

Package 1 Width	32.7 in (83 cm)
------------------------	-----------------

Package 1 Length	26.2 in (66.5 cm)
-------------------------	-------------------

Package weight(Lbs)	44.40 lb(US) (20.14 kg)
----------------------------	-------------------------

Contractual warranty

Warranty (in months)	24
-----------------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Total lifecycle Carbon footprint	49 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	47 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	1 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	0 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	1 kg CO2 eq.

Use Better



Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Compliant By Exemption
REACH Regulation	Free of Substances of Very High Concern above the threshold
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
Halogen content performance	Product contains halogen above thresholds

Use Longer



Lifetime extension

Repair	No
--------	----

Use Again



Repack and remanufacture

Recyclability potential, in %	95
Circularity Profile	End of Life Information
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Image of product / Alternate images

Alternative



